Rex is the multi-frequency pipe & cable locator for all utilities

The sleek, ultralight design of the transmitter is less than 2" thick and weighs less than 4 lbs. At slightly over 7 lbs., the entire **Re**ceiver/**x**mitter system fits easily into a custom shoulder bag.



Optimized for finding

- Water, sewer, and gas pipes
- Electric & telecomm cables













Receiver Specifications	
Operating Frequency:	Active: 512 Hz, 33 kHz and 82 kHz; Passive: 50 or 60 Hz; Sonde: 512 Hz
Battery:	One 9V Battery
Battery Life:	12 Hours (intermittent usage)
Weight (incl. battery):	2.8 lbs (1.25 kg)
Operating Temperature:	-4°F to 140°F (-20°C to 70°C)
Overall Dimensions:	Closed: 17.5" (44 cm); Extended: 27.7" (70 cm)
Max. Depth Capability:	Approximately 19' (5.8 m)
	Sonde mode - approximately 5' - 15' (1.5 m to 4.2 m)
Water and Dust Resistance:	Rated IP54





Slim, Sleek & Powerful Transmitter 3.5 lbs and 1.75" thick

Transmitter Specifications	
Operating Frequency:	512 Hz, 33 kHz and 82 kHz
Operating Modes:	Conductive, Inductive, and Inductive Clamp
Max. Output Power: (Conductive mode @ 1000 Ω load)	512 Hz and 33 kHz: 1/2, 1, 2 or 5 W 82 kHz: 1/2 or 1 W
Battery Type:	Rechargeable NiMH pack (12V)
Battery Life:	8 Hours (intermittent usage)
Charging:	Internal Smart Charger powered by AC/DC power adapter
Dimensions:	10"W x 10.25"D x 1.75" H (25.4 cm x 26 cm x 4.5 cm)
Weight:	3.5 lbs (1.6 kg)
Operating Temp.:	-4°F to 140°F (-20°C to 70°C)
Water and Dust Resistance:	Rated IP54





Copyright © 2018 Schonstedt Instrument Company. All rights reserved. Schonstedt is a subsidiary of SPX Corporation. Due to a policy of continued development, we reserve the right to alter or amend any published specification without notice. This document may not be copied, reproduced, transmitted, modified or used, in whole or in part, without the prior written consent of Schonstedt Instrument Company.

SCHONSTEDT°

Your Local Dealer:

pollardwater.com