


Schedule 80 PVC Technical
Schedule 80 Fittings & Schedule 80 Unions



Double Wye - Reducing

(Continued)

Socket x Socket x Socket x Socket
 Size 3" is 150 psi, all Fabricated Sizes- 100 psi
 Maximum Internal Pressure Rating @ 73°F (23° C)
 C)




Part Number	Size	G	G1	G2	H	H1	H2	L	M	M1	Approx. Wt. (Lbs.)
876-662F ^{2*}	12X2-1/2	15/16	13- 5/8	11-13/16	5- 5/16	15- 5/8	18- 1/16	23- 3/8	14- 1/8	3- 7/16	38.32
876-663F ^{2*}	12X3	1/8	14-15/16	12- 7/8	6- 3/8	16- 9/16	19- 1/8	25- 1/2	14- 1/8	4- 1/8	42.04
876-664F ^{2*}	12X4	5/8	14- 9/16	13- 3/8	6- 7/8	16-13/16	19- 5/8	26- 1/2	14- 1/8	5- 3/16	50.88
876-666F ^{2*}	12X6	2- 5/8	16- 5/8	15- 3/8	8- 7/8	19- 7/8	21- 5/8	30- 1/2	14- 1/8	7- 1/2	68.01
876-668F ^{2*}	12X8	4- 1/4	18- 9/16	17	10- 1/2	22-13/16	23- 1/4	33- 3/4	14- 1/8	9- 5/8	80.90
876-670F ^{2*}	12X10	5- 3/4	20- 3/16	18- 1/2	12	25- 7/16	24- 3/4	36- 3/4	14- 1/8	11-15/16	89.92

² Fiberglass reinforced.
 * Fabricated

Union 2000 - Socket/FKM

Socket x Socket with FKM O-ring Seal
 Dimensions Also Applicable to
 8097-XXX EPDM O-Ring Seals



Pressure Rating
 1/4" - 4" 235 psi @ 73°F
 6" 150 PSI @ 73°F

Part Number	Size	L	M	N	NUT O.D.	Approx. Wt. (Lbs.)
857-002	1/4	1-15/16	15/16	5/8	1-21/32	.09
857-003	3/8	2- 5/32	1- 1/32	19/32	1-25/32	.11
8057-005	1/2	2- 3/32	1- 3/16	11/32	1- 7/8	.12
8057-007	3/4	2- 3/8	1-13/32	3/8	2- 9/32	.19
8057-010	1	2-11/16	1-23/32	7/16	2- 9/16	.26
8057-012	1-1/4	2-15/16	2- 3/32	7/16	3- 3/32	.39
8057-015	1-1/2	3- 1/4	2- 3/8	1/2	3- 1/2	.52
8057-020	2	3-17/32	2- 7/8	17/32	4- 9/32	.86
8057-025	2-1/2	4- 7/32	3- 1/2	25/32	6- 5/32	2.16
8057-030	3	4- 1/4	4- 3/16	1/2	6- 5/32	2.18
8057-040	4	5- 1/8	5- 1/4	5/8	7- 3/4	3.83
8057-060	6	6-27/32	7- 1/2	25/32	11- 5/8	11.46