




## Schedule 80 PVC Technical Schedule 80 Unions

### Union (Old Style) - Special Reinforced Fipt/FKM

Socket x SR Fipt w/FKM O-ring Seal - Stainless Steel Collar  
Dimensions Also Applicable to  
899-XXXSR EPDM O-Ring Seals




Pressure Rating  
235 psi @ 73°F

| Part Number | Size  | L       | M       | N       | NUT O.D. | Approx. Wt. (Lbs.) |
|-------------|-------|---------|---------|---------|----------|--------------------|
| 859-002SR   | 1/4   | 2- 1/16 | 15/16   | 25/32   | 1-21/32  | .12                |
| 859-003SR   | 3/8   | 2- 9/32 | 1- 1/32 | 7/8     | 1-25/32  | .13                |
| 859-005SR   | 1/2   | 2- 9/32 | 1- 9/32 | 21/32   | 1-31/32  | .16                |
| 859-007SR   | 3/4   | 2-19/32 | 1-17/32 | 25/32   | 2- 1/2   | .28                |
| 859-010SR   | 1     | 2-15/16 | 1-27/32 | 25/32   | 2- 7/8   | .39                |
| 859-012SR   | 1-1/4 | 3- 5/32 | 2- 7/32 | 29/32   | 3- 5/16  | .55                |
| 859-015SR   | 1-1/2 | 3-13/32 | 2- 9/16 | 1- 1/32 | 3- 9/16  | .68                |
| 859-020SR   | 2     | 4- 3/32 | 3- 1/32 | 1-19/32 | 4- 3/16  | 1.12               |
| 859-030SR   | 3     | 5- 1/4  | 4- 3/8  | 1-11/16 | 5- 3/4   | 2.55               |
| 859-040SR   | 4     | 5- 7/8  | 5-13/32 | 2- 1/8  | 7- 3/32  | 3.96               |

### Union - Socket/Brass Fipt/FKM

Socket x Fipt with Brass Thread Insert & FKM O-ring Seal  
Dimensions Also Applicable to  
899-XXXBR EPDM O-Ring Seals




Pressure Rating  
235 psi @ 73°F

| Part Number | Size  | L       | M       | N       | NUT O.D. | Approx. Wt. (Lbs.) |
|-------------|-------|---------|---------|---------|----------|--------------------|
| 859-007BR   | 3/4   | 2-11/16 | 1-17/32 | 15/16   | 2- 1/2   | .35                |
| 859-010BR   | 1     | 2-13/16 | 1- 7/8  | 1- 1/32 | 2- 7/8   | .50                |
| 859-012BR   | 1-1/4 | 3- 9/32 | 2- 7/32 | 1- 1/16 | 3- 5/16  | .73                |
| 859-015BR   | 1-1/2 | 3- 1/2  | 2- 9/16 | 1- 3/32 | 3-17/32  | .91                |
| 859-020BR   | 2     | 3- 5/8  | 2- 7/8  | 1- 1/4  | 4- 5/16  | 1.59               |

Not intended to convey or dispense water for human consumption through drinking or cooking

### Union (Old Style) - Fipt/FKM

Fipt x Fipt with FKM O-ring Seal  
Dimensions Also Applicable to  
898-XXX EPDM O-Ring Seals



Pressure Rating  
235 psi @ 73°F

| Part Number | Size | L       | M       | N     | NUT O.D. | Approx. Wt. (Lbs.) |
|-------------|------|---------|---------|-------|----------|--------------------|
| 858-002     | 1/4  | 1-15/16 | 15/16   | 11/16 | 1-21/32  | .09                |
| 858-003     | 3/8  | 2- 5/32 | 1- 1/32 | 15/16 | 1-25/32  | .12                |