


Schedule 80 PVC Technical
Schedule 80 Fittings



22-1/2° EII

Socket x Socket

(Continued)




| Part Number | Size | H | J | M | Approx. Wt. (Lbs.) |
|-------------|-------|----------|---------|----------|--------------------|
| 816-020 | 2 | 1- 7/8 | 3/8 | 2-27/32 | .38 |
| 816-025 | 2-1/2 | 2- 7/32 | 15/32 | 3- 1/2 | .68 |
| 816-025F* | 2-1/2 | 2- 7/8 | 7/8 | 3- 7/16 | .83 |
| 816-030 | 3 | 2-3/8 | 1/2 | 4- 5/32 | .96 |
| 816-040 | 4 | 2- 7/8 | 5/8 | 5- 1/4 | 1.64 |
| 816-045F* | 4-1/2 | 3-13/16 | 1- 5/16 | 5- 5/8 | 2.60 |
| 816-050F* | 5 | 4- 1/8 | 1- 1/8 | 6- 5/16 | 3.14 |
| 816-060 | 6 | 3-15/16 | 7/8 | 7-9/16 | 4.33 |
| 816-060F* | 6 | 4- 5/8 | 1- 3/8 | 7- 1/2 | 5.14 |
| 816-080 | 8 | 5- 1/16 | 1- 1/32 | 9- 3/4 | 8.18 |
| 816-080F* | 8 | 5- 7/8 | 1- 5/8 | 9- 5/8 | 7.06 |
| 816-100F* | 10 | 7- 5/16 | 2- 1/16 | 11-15/16 | 20.59 |
| 816-120F* | 12 | 8- 9/16 | 2- 5/16 | 14- 1/8 | 27.52 |
| 816-140F* | 14 | 9-13/16 | 2-13/16 | 15- 1/2 | 34.64 |
| 816-160F* | 16 | 11- 5/16 | 3- 5/16 | 17-11/16 | 52.97 |
| 816-180F* | 18 | 12- 3/4 | 3- 3/4 | 19- 7/8 | 74.44 |
| 816-200F* | 20 | 14- 1/4 | 4- 1/4 | 22- 1/16 | 106.03 |
| 816-240F* | 24 | 17- 3/16 | 5- 3/16 | 26- 7/16 | 189.95 |

* Fabricated

45° EII

Socket x Socket



| Part Number | Size | H | J | M | Approx. Wt. (Lbs.) |
|-------------|-------|---------|---------|---------|--------------------|
| 817-002 | 1/4 | 13/16 | 5/32 | 27/32 | .02 |
| 817-003 | 3/8 | 15/16 | 3/16 | 1 | .03 |
| 817-005 | 1/2 | 1- 1/8 | 1/4 | 1- 3/16 | .06 |
| 817-007 | 3/4 | 1- 5/16 | 5/16 | 1-13/32 | .09 |
| 817-010 | 1 | 1- 7/16 | 5/16 | 1-23/32 | .29 |
| 817-012 | 1-1/4 | 1- 5/8 | 3/8 | 2- 1/8 | .21 |
| 817-015 | 1-1/2 | 1-13/16 | 7/16 | 2- 3/8 | .30 |
| 817-020 | 2 | 2- 1/8 | 5/8 | 2- 7/8 | .45 |
| 817-025 | 2-1/2 | 2-7/16 | 11/16 | 3- 1/2 | .83 |
| 817-030 | 3 | 2-25/32 | 29/32 | 4-1/8 | 1.11 |
| 817-040 | 4 | 3- 5/16 | 1- 1/16 | 5- 1/4 | 1.99 |