


Schedule 80 PVC Technical
PVC Pipe Flange Dimensions & Information




Flange - Blind



Part Number	Size	R	Bolt Circle Dia.	Bolt Size	Max. O.D.	Min. Bolt Length	No of Bolts	Approx. Wt. (Lbs.)
853-005	1/2	17/32	2- 3/8	1/2	3-17/32	2	4	.20
853-007	3/4	5/8	2- 3/4	1/2	3- 7/8	2	4	.28
853-010	1	3/4	3-1/8	1/2	4-1/4	2-1/4	4	.40
853-012	1-1/4	23/32	3- 1/2	1/2	4- 5/8	2-1/4	4	.37
853-015	1-1/2	23/32	3-27/32	1/2	5- 1/16	2-1/2	4	.49
853-020	2	27/32	4- 3/4	5/8	5-31/32	3	4	.81
853-025	2-1/2	1	5- 1/2	5/8	7	3-1/4	4	1.52
853-030	3	1- 1/16	6	5/8	7- 1/2	3-1/4	4	1.64
853-040	4	1- 5/32	7- 1/2	5/8	9- 1/16	3-1/2	8	2.41
853-060	6	1- 3/8	9- 1/2	3/4	11-1/4	4	8	4.14
853-080	8	1- 7/16	11- 3/4	3/4	13- 1/2	4-1/2	8	6.74
853-100	10	1-11/16	14- 1/4	7/8	16	5	12	11.67
853-120	12	1-11/16	17	7/8	19	5	12	16.96

Flange Van Stone Style IPS (With Plastic Ring)

Socket



Part Number	Size	L	M	N	R	Bolt Circle Dia.	Bolt Size	Max. O.D.	No of Bolts	Approx. Wt. (Lbs.)
854-005	1/2	1- 1/32	1- 7/32	5/32	17/32	2- 3/8	1/2	3- 1/2	4	.18
854-007	3/4	1- 1/8	1- 7/16	5/32	9/16	2- 3/4	1/2	3- 7/8	4	.25
854-010	1	1- 9/32	1- 3/4	5/32	5/8	3- 1/8	1/2	4- 1/4	4	.35
854-012	1-1/4	1-13/32	2- 5/32	5/32	11/16	3- 1/2	1/2	4- 5/8	4	.43
854-015	1-1/2	1-17/32	2- 7/16	3/16	3/4	3- 7/8	1/2	5	4	.55
854-020	2	1-11/16	2-15/16	3/16	13/16	4- 3/4	5/8	6	4	.85
854-025	2-1/2	2	3- 1/2	3/16	31/32	5- 1/2	5/8	7	4	1.42
854-030	3	2- 1/8	4- 1/4	1/4	1- 1/16	6	5/8	7- 1/2	4	1.77
854-040	4	2- 1/2	5- 1/4	1/4	1- 1/8	7- 1/2	5/8	9	8	2.76
854-050	5	3	6- 1/4	3/8	1- 1/8	8- 1/2	3/4	10- 1/8	8	3.29
854-060	6	3- 3/8	7- 9/16	7/16	1- 9/32	9- 1/2	3/4	11	8	4.69
854-080	8	4- 3/8	9- 5/16	9/32	1-3/8	11- 3/4	3/4	13- 1/2	8	6.69
854-100	10	5-11/16	11- 3/4	21/32	1- 5/8	14- 1/4	7/8	16	12	11.68
854-120	12	7- 1/4	13- 3/4	5/8	1-5/8	17	7/8	19	12	17.30
854-140	14	7- 1/2	15- 1/2	1/2	2	18- 3/4	1	21	12	27.24
854-160	16	8- 3/4	17- 3/4	1/2	2- 3/8	21- 1/4	1	23- 1/2	16	39.51
854-180	18	9	20	1/4	2- 3/8	22- 3/4	1- 1/8	25	16	45.97