NQ70M6650DS

30" Microwave Combination Wall Oven



Signature Features

Steam Cook (Oven)

• Delivers moisture at precise times for a crisp, browned outside and tender inside.

Speed Cook (Microwave)

• Cook food faster and more evenly by using power convection.

Dual Convection (Oven)

• Circulates air for faster, more even cooking using true convection.

Available Colors



Stainless Steel (shown)



Black Stainless Steel



Steam Cook



Dual Convection

Features

- 1.9/5.1 cu. ft. Capacity
- Guilding Light Controls
- Hybrid Clean and Self-Clean (Oven)
- Wi-Fi Connectivity
- Wi-Fi Enabled Temperature Probe (Oven)
- LED Spotlights (Oven)
- Easy View Window
- 3 Heavy-Duty Racks including a Gliding Rack (Oven)

- Soft-Close Door (Oven)
- Ceramic Plate (Microwave)
- Rapid Preheat (Oven)
- Auto Latch Microwave Door
- Broil Element
- Smart Control Key (Oven)
- 6 Rack Positions (Oven)
- Drop-Down Door Design

Convenience


- Sabbath Mode (Oven)
- Hidden Heating Element (Oven)
- Delay Start (Oven)
- Convection Conversion
- Child Safety Lock
- Proofing (Oven)
- Warming Mode (Oven)
- Kitchen Timer

30" Microwave Combination Wall Oven


Cabinet Dimensions

Combination Oven Installed in Cabinet

- *Junction Box
- **Allow a minimum of 22" for clearance to adjacent corners, drawers, walls, etc. when door is open.



Product Dimensions



Total Capacity: 1.9/5.1 cu. ft.

Microwave: 1.9 cu. ft.
Wall Oven: 5.1 cu. ft.
Hidden Bake Element
Bake: 175°F-550°F

Convection Bake: 175°F–550°FConvection Roast: 175°F–550°F

• Broil: Low-High

Steam Bake: 230°F-550°FSteam Roast: 230°F-550°F

ProofingSabbath Mode

Warranty

One (1) Year All Parts and Labor

Product Dimensions & Weight (WxHxD)

Outside (Max) Combination Oven Dimensions: $29^{7}/_{8}$ " x $43^{1}/_{4}$ " x $25^{11}/_{16}$ "

Combination Oven Cut-Out Dimensions: $28^{1}/_{2}$ " x $42^{1}/_{4}$ " x $23^{1}/_{2}$ "

Weight: 119 lbs.

Shipping Dimensions & Weight (WxHxD)

Dimensions:

33⁵/₈" x 48³/₁₆" x 29⁵¹/₆₄"

Weight: 132.5 lbs.

Color	Model#	UPC Code
Stainless Steel	NQ70M6650DS	887276195148
Black Stainless Steel	NQ70M6650DG	887276195124

RATING		
240V	8.2 kW	
208V	6.1 kW	
BREAKER SIZE		
240V	40 Amps	
208V	30 Amps	