MEDMCW31WS 30-INCH TRIPLE COMBINATION BUILT-IN OVEN WITH SPEED OVEN MASTERPIECE® SERIES





Home Connect



FEATURES & BENEFITS

- \star First triple combination oven with speed oven in the market
 - Designed for flexibility—standard or flush installation into kitchen cabinets
 - Specially crafted gray glass on stainless steel for a luxurious look and finish
 - Speed oven with microwave capability can broil and convection bake
 - Large commercial style rotisserie with 12 pound capacity

ACCESSORIES (INCLUDED)

Upper Cavity: Metal Turntable, Rack, Ceramic Tray; Lower Cavity: 3 Telescopic Racks, Multi-point Meat Probe, Max Broil Pan, Rotisserie

WARRANTY

Limited Warranty Parts and Labor

2 Year

GENERAL PROPERTIES

Heating Modes – Upper Cavity

36 CookSmart[™] Auto Programs (including True Convection, Speed Convection, Broil, Convection Broil, Keep Warm) and Heating Programs and Microwave Programs

Heating Modes – Lower Cavity

(16) Bake, Broil, Max Broil, Roast, Convection Bake, Convection Broil, Max Convection Broil, Convection Roast, Proof, Warm, Pizza, True Convection, Dehydrate, Speed Convection, Slow Roast, Rotisserie


	- ,	
Sabbath		Yes
Warming Drawer		Yes
Cleaning Type – Lower Cavity		Easy Clean and Self Clean
Telescopic Rack(s)		3
Illumination Type	Upper Cavity Lower Cavity	LED Halogen
Interior Lights	Upper Cavity Lower Cavity	1 2
Home Connect (Wi-Fi Enabled)		Yes, Lower Oven Only
OVEN PERFORMANCE	:	
Microwave Power		1,000 W
Bake / Broil Element	Upper Cavity Lower Cavity	600 W / 1,750 W 2,400 / 1,000 / 3,800 W
Convection Element	Upper Cavity Lower Cavity	1,700 W 2,000 W
Warming Drawer		450 W
TECHNICAL DETAILS		
Watts		10,200 W
Circuit Breaker		50 A
Volts; Frequency		240 / 208 V; 60 Hz
Plug Type		Fixed Connection, No Plug
Conduit		60" 4-Wire
Energy Source		Electric
DIMENSIONS & WEIG	нт	
Overall Appliance Dimensions (HxWxD)		61 3/16" × 29 3/4" × 24 1/2"
Trim Overlaps (Top – Sides – Bottom)		1/2 " - 9 /16" - 0"
Required Cutout Size (HxWxD) – Standard		60 3/4 " x 28 1/2 " x 23 1/2 "
Required Cutout Size (HxWxD) – Flush		61 5/16 " x 30" x 24 1/2 "
Speed Oven Capacity		1.6 cu. ft.
Oven Capacity		4.5 cu. ft.
Warming Drawer Capacity		2.5 cu. ft.
Overall Lower Oven Interior Dimensions (HxWxD)		17 3/4 " × 24" × 17 7/8 "
Usable Lower Oven Interior Dimensions (HxWxD)		13 1/2 " x 21 5/8 " x 16 1/4 "

THERMADOR® EXCLUSIVE

MEDMCW31WS 30-INCH TRIPLE COMBINATION BUILT-IN OVEN WITH SPEED OVEN MASTERPIECE® SERIES



30-INCH TRIPLE COMBINATION OVEN WITH SPEED OVEN AND WARMING DRAWER



These warranties give you specific legal rights and you may have other rights that vary from state to state. Full warranty and limited warranty from date of installation. For complete warranty details, refer to your Use & Care manual, or ask your dealer.

__ 24¹/2" __ (622 mm)

measurements in inches (mm)

Specifications are for planning purposes only. Refer to installation instructions and consult your countertop supplier prior to making counter opening. Consult with a heating and ventilation engineer for your specific ventilation requirements. For the most detailed information, refer to installation instructions accompanying product or write to Thermador indicating the model number. Specifications are correct at time of printing. Thermador reserves the right to change product specifications or design without notice. Some models are certified for use in Canada. Thermador is not responsible for products that are transported from the U.S. for use in Canada.

1 800 735 4328 | USA THERMADOR.COM | CANADA THERMADOR.CA | ©2020 BSH HOME APPLIANCES CORPORATION. ALL RIGHTS RESERVED.