## PF1500 Series

# Low-Consumption Toilet Calhoun series



### **Product Features**

- 1.6 GPF HET, Low-Consumption Toilet
- Gravity fed, jetted box rim
- 2" fully glazed trapway
- High performance 3" flush valve
- 9" x 7" water surface
- Close coupled tank with cover
- Quick connect, two-bolt tank-to-bowl installation

#### • Chrome flush lever

- Available in round front, elongated and ADA elongated
- Seat and supply not included
- Anti-siphon fill valve
- · Sanitary bar on all bowls



#### PF1503WH/PF6112KWH

#### **Codes and Standards**

- ADA (PF1503WH)
- IAPMO/cUPC
- ASME A112.19.2 / CSA B45.1-13
- MaP tested 1000g

#### Model Numbers

PF1500WH	Round Front Bowl, White			
PF1501WH	Elongated Bowl, White			
PF1502FWH	Elongated, LargeFootprint Bowl, White			
PF1503WH	ADA Height Bowl, White			
PF6112KWH	1.6 Tank w/ 12" RI for PF1500 series			
PF6110KWH	1.6 Tank w/ 10" RI for PF1500 series			
PF6114KWH	1.6 Tank w/ 14" RI for PF1500 series			
PF6112RKWH	1.6 RH Tank w/ 12" RI for PF1500 series			




### PF1500 Series

# Low-Consumption Toilet **Calhoun series**

#### **Product Specification**

The combination toilet shall be made of vitreous china. Toilet shall be 1.6 gpf (6 lpf). Toilet shall have 2" (5.1cm) fully glazed trapway. Toilet shall include a chrome or white trip lever. Toilet shall be less seat and supply. Toilet shall be ADA compliant (PF1503) with 17" high bowl.

	RF	EL	EL	ADA
	PF1500/PF6112K2	PF1501/PF6112K	PF1502F/PF6112K	PF1503/PF6112K2
Α	30"	30"	31-1/8''	31-1/2"
В	16-1/2"	18-1/2"	18-1/2''	18-1/2"
C	15-1/2"	15-1/2"	16-1/2''	17"
D	27"	29"	29''	29-1/4"
E	10"	9-7/8"	12''	10"
F	20-5/8"	21-3/8"	25''	21"
G	8"	8"	8''	8"
Н	12"	12"	12''	12"
	PF1500/PF6110K	PF1501/PF6110K	PF1502F/PF6110K	PF1503/PF6110K
D	26-1/4"	27-7/8"	27-3/4"	28-1/8"
G	6-3/4"	6-3/4"	6-3/4"	6-3/4"
Н	10"	10"	10"	10"
	PF1500/PF6114K	PF1501/PF6114K	PF1502F/PF6114K	PF1503/PF6114K
D	29-7/8"	31-3/8"	31-1/8"	31-3/8"
G	10-1/4"	10-1/4"	10-1/4"	10-1/4"
н	14"	14"	14"	14"





Note: All dimensions and specifications are nominal and may vary: Dimensions of 8" and greater have a tolerances of +3%. Dimensions less than 8" have a tolerances of +5%.

#### Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO fixtures carry a limited lifetime warranty on the vitreous china and a 5-year limited warranty on the parts and fittings. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless we agree in writing to do otherwise.

