FS1106HD



## **SERIES FS1100HD** FIBERGLASS STEPLADDER



OSHA





duty inside

Heavy duty reinforcement plates.

spreader braces.

Molded top with



Double-rivet step construction with heavy-duty gusset bracing.  $\textbf{SHOX}^{\scriptscriptstyle{\mathsf{TM}}}\mathbf{-}\mathsf{Advanced}$ 



impact absorption protects fiberglass rails against damage.

6. Full Metal Boot™.

TYPE IAA	
<b>375</b> LB	S.
<b>3/3</b> L0	AD CAPACITY
INCLUDES WEIGHT OF US	SER PLUS MATERIALS

MODEL	LADDER Size	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. CUBES
FS1104HD	41	8' 6"	20 3/8"	28 1/2"	19	4.2'
FS1106HD	6'	10' 5"	24"	42"	27	7.4'
FS1108HD	8'	12' 4"	27 3/8"	52 3/4"	36	11,4'
FS1110HD	10'	14' 3"	31"	64 3/8"	45	15.9'
FS1112HD	12'	16' 2"	<sup>34</sup> 9/ <sub>16</sub> "	76 1/4"	56	20.4'

Add suffix -S51 to model number for optional molded Pail Shelf. Available on all sizes and most step models.

FS1306HD



## SERIES FS1300HD

TYPE IAA LBS.

LOAD CAPACITY



OSHA





Heavy-duty gusset bracing.





5. Slip-resistant boot.



MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. Cubes
FS1304HD	41	8' 6"	18 7/8"	29 1/8"	15	3.7'
FS1305HD	5'	9' 5"	20 3/8"	34 7/8"	18	4.6'
FS1306HD	6'	10' 5"	21 3/4"	41 1/8"	21	6.5'
FS1308HD	81	12' 3"	24 3/4"	54"	28	9.7'
FS1310HD	10'	14' 2"	27 7/8"	66 1/4"	40	13.8'
FS1312HD	12'	16' 1"	31"	77"	51	18.4'





**SERIES FS1400HD** FIBERGLASS STEPLADDER

TYPE IAA LBS. LOAD CAPACITY



OSHA







braces.



Riveted step construction with gussets.



protects fiberglass rails against damage. Raptor Boot™ -

 $\textbf{SHOX}^{\scriptscriptstyle{\text{TM}}} - \text{Advanced}$ 

impact absorption



Heavy duty boot protects fiberglass.

MODEL	LADDER SIZE	MAX. REACH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WEIGHT (LBS)	APPROX. CUBES
FS1403HD	3'	7' 6"	17 3/4"	23 7/8"	12	2.6'
FS1404HD	41	8' 6"	19 1/4"	28"	15	3.7'
FS1405HD	5'	9' 5"	20 7/8"	34 1/8"	17	5'
FS1406HD	6'	10' 5"	22 1/8"	39 3/8"	21	6.41
FS1407HD	7'	11' 4"	24 1/16"	46 13/16"	25	7.5'
FS1408HD	8'	12' 3"	25 1/8"	52 ½"	26	9.5'
FS1410HD	10'	14' 2"	28 3/4"	65"	42	13,6'
FS1412HD	12'	16' 1"	32 3/8"	76 1/8"	53	21.8'