
SMALL DIAMETER DUAL WALL FABRICATED REDUCING CROSS TEES 6" X 4" - 12" X 10" DIAMETER

REDUCING CROSS TEES

	PART #	PIPE SIZE	А	В	С	JOINT
**	0630AN	6 x 4 in	14.7 in	9.9 in	14.7 in	*
		(150 x 100 mm)	(374 mm)	(252 mm)	(374 mm)	
**	0830AN	8 x 4 in	17.3 in	11.2 in	17.3 in	*
	UUUUAN	(200 x 100 mm)	(439 mm)	(285 mm)	(439 mm)	
**	0831AN	8 x 6 in	20.2 in	11.5 in	20.2 in	*
		(200 x 150 mm)	(512 mm)	(293 mm)	(512 mm)	
**	1030AN	10 x 4 in	20.2 in	11.3 in	20.2 in	*
		(250 x 100 mm)	(512 mm)	(286 mm)	(512 mm)	
**	1031AN	10 x 6 in	20.2 in	13.1 in	20.2 in	*
		(250 x 150 mm)	(512 mm)	(332 mm)	(512 mm)	
**	10224N	10 x 8 in	22.7 in	15.2 in	22.7 in	*
	1032AN	(250 x 200 mm)	(576 mm)	(385 mm)	(576 mm)	
	1000 4 1	12 x 4 in	30.7 in	13.6 in	30.7 in	*
	1230AN	(300 x 100 mm)	(780 mm)	(345 mm)	(780 mm)	
	1231AN	12 x 6 in	30.7 in	14.5 in	30.7 in	*
	1231AN	(300 x 150 mm)	(780 mm)	(368 mm)	(780 mm)	
	1232AN	12 x 8 in	30.7 in	17.0 in	30.7 in	*
	1232AN	(300 x 200 mm)	(780 mm)	(432 mm)	(780 mm)	
	1233AN	12 x 10 in	30.7 in	16.4 in	30.7 in	*
		(300 x 250 mm)	(780 mm)	(416 mm)	(780 mm)	



** LIMITED AVAILABILITY. PLEASE SEE INJECTION MOLDED FITTING SECTION FOR OTHER AVAILABLE FITTINGS

* = PLAIN END

NOTE: ALL FITTINGS DIMENSIONS ARE FOR REFERENCE ONLY



DRAWING #:	2455	
DRAWN BY:	JCB	05.09.07
APPROVED BY:	JCB	06.28.07
REVISIONS:	TJR	1/29/2010