### **USB** Rechargeable **Hard Hat Headlamp Kit**

2111-21

Lumens	475 / 300 / 300 / 150 / 25
Modes	Spot/Flood, Spot – High, Flood – High/Medium/Low
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB

**Includes:** (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord, Hard Hat Clips



POWERED BY
REDLITHIUM' USB
RECHARGEABLE

# **USB** Rechargeable **700L Focusing Flashlight Kit**

2110-21

Lumens	700 / 100 / 700
Modes	High, Low, Strobe
Spot Beam Distance	155 m
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	6.5"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery Pack, 2 ft Heavy Duty USB Cord





2112-21

Lumens	445 / 100
Modes	High, Low
Hands-Free	Dual Magnets
Water & Dust Rating	IP54
Height	6.0"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord





# **USB** Rechargeable **Low-Profile Headlamp Kit**

2115-21

Lumens	600 / 350 / 125 / 25
Modes	High, Medium, Low, Eco
Battery Position	Rear
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB

**Includes:** (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord, (4) Hard Hat Clips



POWERED BY
REDLITHIUM
USB
RECHARGEABLE

# **USB** Rechargeable **Pivoting Flashlight Kit**

2113-21

Lumens	500 / 400 / 100
Modes	Spot - High, Flood - High, Flood - Low
Spot Beam Distance	155 m
Pivoting Head	110°
Water & Dust Rating	IP54
Height	6.3"
Powered By	REDLITHIUM™ USB

**Includes:** (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord

# **USB Rechargeable BEACON™ Hard Hat Light Kit**

2116-21

Lumens	600 / 400, 200, 25 / 400
Modes	Spot/Flood, Flood - High/ Medium/Low, Spot - High
BEACON™ Mode	Steady & Blinking
Spot Beam Distance	125 m
Water & Dust Rating	IP54
Powered By	REDLITHIUM™ USB

**Includes:** (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord, (2) Hard Hat Clips



# **USB Rechargeable ROVER**™ **Pivoting Flood Light Kit**


2114-21

Lumens	550 / 250 / 100
Modes	High, Medium, Low
Pivoting Head	210°
Water & Dust Rating	IP54
Height	4.4"
Powered By	REDLITHIUM™ USB

Includes: (1) REDLITHIUM™ USB Battery, 2 ft Heavy Duty USB Cord







# **USB** Rechargeable **Utility Hot Stick Light Kit**

2119-22

Lumens	350 / 100
Modes	Flood – High/Low
kV Rating	100kV
Water & Dust Rating	IP67
Height / Length	0.5" / 7.4"
Powered By	REDLITHIUM™ USB



**Includes:** (2) REDLITHIUM™ USB Batteries, 2 ft Heavy Duty USB Cord, REDLITHIUM™ USB Charger & Portable Power Source, 12V DC Vehicle Plug, 2.1A Wall Plug

# **REDLITHIUM™ USB Battery**

48-11-2130

#### Specifications:

Amp Hours	2.4
Cell Chemistry	LITHIUM-ION
Voltage	4V





#### **USB Rechargeable Portable Power Source and Charger**

48-59-2012

#### **Specifications:**

Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes
USB Charging Port	2.1A USB Charging Port for External Devices
Height	3.9"

Includes: REDLITHIUM™ USB Portable Power Source and Charger, 2 ft Heavy Duty USB Cord

#### **USB Rechargeable Portable Power Source and Charger Kit**

48-59-2013

#### **Specifications:**

Cell Chemistry	LITHIUM-ION
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes
USB Charging Port	2.1A USB Charging Port for External Devices
Height	3.9"

**Includes:** (1) REDLITHIUM™ USB Battery, REDLITHIUM™ USB Portable Power Source and Charger, 2 ft Heavy Duty USB Cord

## **MILWAUKEE®** Penlight

Lumens	100
Water & Dust Rating	IP67
Height	5.4"
Powered By	(2) AAA

Includes: (2) AAA Batteries

2105





# **325L Focusing Flashlight**

Includes: (4) Hard Hat Clips, (3) AAA Batteries

**MILWAUKEE®** Spot/Flood

450 / 350, 150, 25 / 350

Spot/Flood, Flood - High/ Medium/Low, Spot

Headlamp

Spot Beam Distance

Water & Dust Rating

Powered By

2104

Lumens

Modes

2107

2101	
Lumens	325 / 25
Modes	High, Low
Spot Beam Distance	115 m
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP67
Height	5.0"
Powered By	(3) AAA

100 m

IP54 (3) AAA

Includes: (3) AAA Batteries

2107S Also Available, Includes Holster

# **MILWAUKEE® Headlamp**

2103	
Lumens	350 / 150 / 25
Modes	High, Medium, Low
Impact Rating	2 m
Water & Dust Rating	IP54
Powered By	(3) AAA

Includes: (4) Hard Hat Clips, (3) AAA Batteries

# **ROVER**<sup>™</sup> Magnetic Flood Light

Lumens	300 / 100
Modes	High, Low
Water & Dust Rating	IP54
Height	4.8"
Powered By	(2) AA

Includes: (2) AA Batteries



