



M18™ FORCE LOGIC™ 750 MCM Crimper Kit

2779-22, 2779-750A, 2779-750C

Specifications:

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length / Weight	16.0" / 11.5 lbs

Includes: 2779-750A 49-12-KITA; 2779-750C 49-12-KITC;

All Kits Include: 2779-22 (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, Multi-Voltage Charger, Carrying Case

Related Accessories:

Accessory Kits

49-12-KITC EXACT™ #6 AWG – 750 MCM Cu 12T U Style Die Kit;

49-12-KITA EXACT™ #6 AWG – 750 MCM Al 12T U Style Die Kit

EXACT™ 12T Copper U Style Dies

49-12-U001C #1 Copper 12T U Style Die;

49-12-U002C #2 Copper 12T U Style Die;

49-12-U004C #4 Copper 12T U Style Die;

49-12-U006C #6 Copper 12T U Style Die;

49-12-U008C #8 Copper 12T U Style Die;

49-12-U01AC 1/0 Copper 12T U Style Die;

49-12-U02AC 2/0 Copper 12T U Style Die;

49-12-U03AC 3/0 Copper 12T U Style Die;

49-12-U04AC 4/0 Copper 12T U Style Die;

49-12-U250C 250 MCM Copper 12T U Style Die;

49-12-U300C 300 MCM Copper 12T U Style Die;

49-12-U350C 350 MCM Copper 12T U Style Die;

49-12-U400C 400 MCM Copper 12T U Style Die;

49-12-U500C 500 MCM Copper 12T U Style Die;

49-12-U600C 600 MCM Copper 12T U Style Die;

49-12-U750C 750 MCM Copper 12T U Style Die

EXACT™ 12T Aluminum U Style Dies

49-12-U001 #1 Aluminum 12T U Style Die;

49-12-U002 #2 Aluminum 12T U Style Die;

49-12-U004 #4 Aluminum 12T U Style Die;

49-12-U006 #6 Aluminum 12T U Style Die;

49-12-U008 #8 Aluminum 12T U Style Die;

49-12-U01A 1/0 Aluminum 12T U Style Die;

49-12-U02A 2/0 Aluminum 12T U Style Die;

49-12-U03A 3/0 Aluminum 12T U Style Die;

49-12-U04A 4/0 Aluminum 12T U Style Die;

49-12-U250 250 MCM Aluminum 12T U Style Die;

49-12-U300 300 MCM Aluminum 12T U Style Die;

49-12-U350 350 MCM Aluminum 12T U Style Die;

49-12-U400 400 MCM Aluminum 12T U Style Die;

49-12-U500 500 MCM Aluminum 12T U Style Die;

49-12-U600 600 MCM Aluminum 12T U Style Die;

49-12-U750 750 MCM Aluminum 12T U Style Die



M18™ FORCE LOGIC™ 15T Crimper Kit

2879-22 (2879-20 Tool-Only)

Specifications:

Crimping Capacity	#8 - 1500 MCM Cu, #8 - 1250 MCM Al
Output Force	15 Tons
Adaptive Pressure Control	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Dimensions (L x W x H)	23.3" x 3.1" x 5.5"
Weight	16.1 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, P-to-U Die Adapter, Carabiner, Multi-Voltage Charger, Contractor Bag

Related Accessory:

49-15-PUAD P-to-U Die Adapter;

49-15-P750 15T 750 MCM Al P-Die;

49-15-P800 15T 800 MCM Al P-Die;

49-15-P000 15T 1000 MCM Al P-Die;

49-15-P750C 15T 750 MCM Cu P-Die;

49-15-P800C 15T 800 MCM Cu P-Die;

49-15-P000C 15T 1000 MCM Cu P-Die



M18™ FORCE LOGIC™ 10,000 PSI Hydraulic Pump Kit

2774-21HD (2774-20 Tool-Only)

Specifications:

Operating Pressure	10,000 psi / 700 bar
Usable Oil Capacity	1.4 qts
Flow Rate at Low Pressure	125.0 in³/min
Flow Rate at High Pressure	25.6 in³/min
Ingress Protection	IP54
Dimensions (L x W x H)	15.8" x 11.5" x 13.9"
Weight	29.7 lbs

Includes: (1) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack, Rapid Charger

Related Accessories:

49-12-2776 Bucket Hanger;

49-12-2775 6' Controller Extension



M18™ FORCE LOGIC™ Cable Cutter Kit w/ 750 MCM Cu Jaws

2672-21

Specifications:

Cut Capacity	750 MCM Cu, 1000 MCM Al
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	5.4" / 14.0"

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, 750 MCM Cable Cutter Jaw, Allen Wrench, Multi-Voltage Charger, Carrying Case



M18™ FORCE LOGIC™ Cable Cutter Kit w/ 477 ACSR Jaws

2672-21S

Specifications:

Cut Capacity	477 HEN ACSR
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	5.4" / 14.0"

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, 477 ACSR Cutting Jaw, Carabiner, Allen Wrench, Multi-Voltage Charger and Inverter, Bucket Bag



M18™ FORCE LOGIC™ Cable Cutter Kit w/ Fine Stranded Wire Jaws

2672-21F

Specifications:

Cut Capacity	777.7 MCM Fine Stranded Wire
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	5.4" / 14.0"

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, Fine Stranded Wire Cutting Jaw, Allen Wrench, Multi-Voltage Charger, Carrying Case



FORCE LOGIC™ Cable Cutter Accessories

Compatible with 2672-21, 2672-21S and 2672-21F

Cutter Jaws

49-16-2772 750 MCM Cu/Al Cutting Jaw;

49-16-2773 477 ACSR Cutting Jaw;

49-16-2777 1/2" EHS Guy Wire Cutting Jaw;

49-16-2778 Fine Stranded Wire Cutting Jaw

Cutter Replacement Blades

48-44-0411 Copper Replacement Blades;

48-44-0412 ACSR Replacement Blades;

48-44-2777 1/2" EHS Guy Wire Replacement Blades;

48-44-2778 Fine Stranded Wire Replacement Blades

M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit w/ Wireless Remote

2776R-21

Specifications:

Cut Capacity	1500 MCM Cu 15kV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	12.4" / 20.8"
Weight	15.8 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Remote, Carabiner, Multi-Voltage Charger and Inverter, Utility Bag

Related Accessory:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit

2776-21

Specifications:

Cut Capacity	1500 MCM Cu 15kV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	12.4" / 20.8"
Weight	15.8 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Carabiner, Multi-Voltage Charger and Inverter, Utility Bag

Related Accessory:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ 1590 ACSR Cutter Kit

2777-21

Specifications:

Cut Capacity	Up to 1590 Falcon ACSR
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Height / Length	10.6" / 16.8"
Weight	11.8 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Carabiner, Side Handle, Multi-Voltage Charger and Inverter, Utility Bag

Related Accessory:

49-16-2775 1590 ACSR Replacement Blades

