CORDED POWER TOOLS



DWE305



13 Amp Reciprocating









12 Amp Reciprocating Saw Kit

12 Amp Reciprocating Saw Kit

12 Amp Compact Reciprocating Saw

Saw Kit	Saw Kit	Saw Kit	Reciprocating Saw
DW311K	DW310K	DWE305K	DWE357
13 Amps	12 Amps	12 Amps	12 Amps
0 - 2,700 spm	0 - 2,700 spm	0 - 2,900 spm	0 - 2,800 spm
1-1/8"	1-1/8"	1-1/8"	1-1/8"
Twist	Twist	Lever	Lever
No	No	Yes	Yes
Yes	Yes	No	No
Yes	Yes	Yes	Yes
Yes	No	No	No
Yes	No	No	No
Yes	No	Yes	Yes
	Saw Kit DW311K 13 Amps 0 - 2,700 spm 1-1/8" Twist No Yes Yes Yes Yes Yes	Saw Kit Saw Kit DW311K DW310K 13 Amps 12 Amps 0 - 2,700 spm 0 - 2,700 spm 1-1/8" 1-1/8" Twist Twist No No Yes Yes Yes Yes Yes No Yes No Yes No	Saw Kit Saw Kit Saw Kit DW311K DW310K DWE305K 13 Amps 12 Amps 12 Amps 0 - 2,700 spm 0 - 2,700 spm 0 - 2,900 spm 1-1/8" 1-1/8" 1-1/8" Twist Twist Lever No No Yes Yes Yes No Yes Yes Yes Yes No No Yes No No Yes No No Yes No No





RECIPROCATING SAWS









CIRCULAR

8-1/4" (210 mm) Circular Saw with

7-1/4" (184 mm) Circular Saw with

7-1/4" (184 mm) **Worm Drive Circular Saw**

7-1/4" (184 mm) Lightweight

blade wrench

7-1/4" (184 mm) Lightweight Circular Saw w/ Electric Brake

Dust collection adapter

	neal FIVUL	neal Fivol	Olloului Out	Gilculai Saw	W/ Elecule blake	
SPECIFICATION	S DW384	DW364	DWS535 / DWS535T	DWE575	DWE575SB	DWE575DC
Amps	15 Amps	15 Amps	15 Amps	15 Amps	15 Amps	-
Max Watts Out	2,075 W	2,075 W	2,100 W	1,950 W	1,950 W	-
No Load Speed	5,800 rpm	5,800 rpm	4,800 rpm	5,200 rpm	5,200 rpm	-
Bevel Capacity	50°	50°	53°	57°	57°	_
Bevel Stops	N/A	N/A	45° / 22.5°	45° / 22.5°	45° / 22.5°	-
Rear Pivot	Yes	Yes	No	No	No	_
Electric Brake	Yes	Yes	No	No	Yes	-
Blade Diameter	8-1/4"	7-1/4"	7-1/4"	7-1/4"	7-1/4"	-
Depth Of Cut At 90°	° 2-15/16"	2-7/16"	2-7/16"	2.55"	2.55"	-
Depth Of Cut At 45	° 2-1/4"	1-7/8"	1-7/8"	1-7/8"	1-7/8"	1-7/8"
Includes (Carbide tipped blade and	Carbide tipped blade and	Carbide tipped 7-1/4" blade,	Carbide tipped	Carbide tipped 7-1/4"	Replacement lower guard
	blade wrench	blade wrench	blade wrench / carbide	7-1/4" blade and	blade and blade wrench	lever and fastening screws

tipped 7-1/4" blade, blade wrench, pre-installed w/ twistlock plug







.lin Saw Kit



Compact Jig Saw Kit

	oig oaw Kit	
SPECIFICATIONS	DW331K	DW317K
Amps	6.5 Amps	5.5 Amps
Strokes/Min	500 - 3,100 spm	0 - 3,100 spm
Stroke Length	1"	1"
Keyless Blade Clamp	Yes	Yes
Dust Blower	Yes	No
Orbital Action	4-position	4-position
Tool Weight	6.4 lbs	6.2 lbs





SPECIFICATIONS	DW788	
Amps	1.3 Amps	-
Strokes/Min	400 - 1,750 spm	- 1
Stroke Length	3/4"	
Depth of Cut (inches)	2"	
Tool Weight	56 lbs	· `
Includes	Hex wrench and blades	(

SCROLL SAW ATTACHMENTS		
F	DW7880 - Scroll Saw Stand	
	DW7881 - Scroll Saw Worklight	



MULTI-TOOL



Oscillating Multi-Tool Kit

SPECIFICATIONS	DWE315K
Amps	3.0 Amps
Oscillations/Min	0 - 22,000 opm
Variable Speed	Yes
Keyless Accessory Ch	ange Yes
LED Light	Yes
Accessories Included	29
Tool Weight	3.1 lbs
Includes DEWAL	T Oscillating Tool Guide System, bi-metal plunge

cut blade, fast-cut wood blade, semi-circle flush cut blade, sanding pad, (25) sheets of sand paper, accessory storage box and multi-brand accessory adaptor