

ANCHORAGE CONNECTORS



RA30-1/



496/



8816-14/



9065/BK

Temporary Anchors


| SKU | Description |
|-----------|--|
| 17D-1/ | Steel twist-lock carabiner; 1-in. gate opening |
| 18D-1/ | Large, steel twist-lock carabiner; 2-in. gate opening. |
| 18D-2-Z7/ | Large, aluminum twist-lock carabiner; 2-1/4-in. gate opening |
| RA30-1/ | Reusable chain with 'O' ring; steep-pitched or flat roof |
| 9065 /BK | Lightweight beam trolley adjusts to fit beam flanges from 3-in. to 4-1/2-in. wide. The adjustable trolley slides along with the worker to provide maximum mobility |
| 496/ | Miller Grip™ portable/reusable anchorage supports 5,000 lb. ultimate strength; for single user connection; 400 lbs. maximum capacity; color-coded green. Hole diameter – 3/4-in. |
| 8816-14/ | Lightweight, adjustable ShadowLite™ Beam Anchor – high-strength aluminum and bronze; 4.2 lbs.; 3-in. to 14-in. |
| 8815-12/ | Lightweight, fixed ShadowLite™ Beam Anchor – stainless steel and high-strength aluminum; 7.7 lbs; 4-in. to 12-in. |

All models shown include connectors with 3,600-lb. gate-strength



RA40/

RA41/



RA45/



416/



417/

Permanent Roof Anchors

| SKU | Description |
|-------|---|
| RA40/ | Double D™ permanent roof anchor is designed to provide two (2) D-ring anchorage points when securely installed on a wood roof sub-surface ridge peak; Complete with 8, 16d nails |
| RA41/ | Single D™ permanent roof anchor is designed to provide one (1) D-ring anchorage point when securely installed on a wood roof sub-surface ridge peak or vertical wall; Complete with 8, 16d nails |
| RA45/ | The Claw™ permanent roof anchor is designed to provide a single anchorage point when securely installed on a wood rafter or truss member; Fits wood sizes 2-in. x 4-in., 2-in. x 6-in., 2-in. x 8-in., 2-in. x 10-in. or 2-in. x 12-in. |
| 416/ | D-Bolt Anchor for up to 4-in. working thickness includes a 5/8-in. diameter bolt with lock washer and nut |
| 417/ | D-Bolt Anchor without hardware |

Miller Swivel Anchors

- Provides freedom of movement with innovative swivel design that offers 360° D-ring rotation & 180° flip
- Options available for use in concrete and steel with 5,000-lb. (5K) and 10,000-lb. (10K) tensile strength
- Available in zinc-plated steel or stainless steel construction
- Rated for up to a 310-lb. (141-kg) user



| SKU | Description |
|-----------------|---|
| RACSWY050C | 5K Zinc-Plated Swivel Anchor w/ Concrete Mounting Hardware |
| RACSWY050S | 5K Zinc-Plated Swivel Anchor w/ Steel Mounting Hardware |
| RACSWYS100C-316 | 5K Stainless Steel Swivel Anchor w/ Concrete Mounting Hardware |
| RACSWYS100S-316 | 5K Stainless Steel Swivel Anchor w/ Stainless Steel Mounting Hardware |
| RACSWY100C | 10K Zinc-Plated Swivel Anchor w/ Concrete Mounting Hardware |
| RACSWY100S | 10K Zinc-Plated Swivel Anchor w/ Steel Mounting Hardware |

