

## UTILITY WORKSHOP VISES

### **FEATURES**

- Vise features a swivel base for flexibility.
- Good value, reliable model for the price.
- Rubber washers on the handle reduce finger pinching injuries.

Heavy-duty design strengthens this ideal utility workshop vise. Cast vises with pipe jaws, anvil and horn feature a swivel base with positive locking in addition to replaceable, hardened steel, serrated jaw facings for user convenience. **26B** is the strongest vise of the utility vise line; consider it for larger workloads. These quality vises are imported.

Catalog No.	Item Code	Throat Depth*		Jaw \	Width	Jaws	Open <sup>Ω</sup>	Weight**	
		in	mm	in	mm	in	mm	lbs	kg
24 1/2C	01522	2 1/2	64	4 1/2	115	4	102	18.0	8.2
25 1/2C	01532	3	76	5 <sup>1</sup> / <sub>2</sub>	140	5	127	27.0	12.3
26 1/2C	01542	3 3/8	86	6 <sup>1</sup> / <sub>2</sub>	165	6	152	41.0	18.6
26B	01545	4 3/16	120	6	150	6	152	60.0	27.3

<sup>\*</sup>See illustration

## **MID-LINE VISES**

#### **FEATURES**

- Mid-level pricing for a well-made, durable vise.
- The vise screw and nut are enclosed to keep out dirt, and they are permanently lubricated.
- Rubber washers on the handle reduce finger pinching injuries.

Mid-line vises are of strength and price between the Combination Vise and Utility Vise. Design features a machined work surface. The main screw and nut are totally enclosed to keep out dirt and eliminate wear. Straight line pull through the bar and the body greatly reduces wear on main vise nut. Mid-line vises are imported and have replaceable, hardened steel jaw facings and replaceable pipe jaws which are serrated and heat-treated. The base swivels 360° and has two swivel base locking clamps with toothed engagement.

	Catalog No.	Item	Throat Depth*		Jaw \	Width	Jaws	Open <sup>Ω</sup>	Pipe Capacity	Weight	
		Code	in	mm	in	mm	in	mm	in-nom.	lbs	kg
	704**	01385	3.45	88	4	102	4.5	114	1/2 - 2	36.0	16.4
	705**	01387	3.75	95	5	127	5.5	140	1/4 - 2 1/2	47.0	21.4
	706**	01389	4.10	104	6	152	5.7	146	1/4 - 3 1/2	61.0	27.7
H	708**	01390	4.75	120.7	8	203	8.25	209.6	1/4 - 3 1/2	91.5	41.6



\*See illustration

# **COMBINATION BENCH & PIPE VISE**


#### **FEATURES**

- Top-of-the line vise for maximum durability.
- Deepest throat of all Reed bench vises.

Designed to provide decades of service, these cast Combination Bench & Pipe Vises carry Reed's lifetime warranty. Steel pipe jaws made of heat-treated, hardened steel are double-sided to reverse jaws once before replacement. Jaw facings are replaceable, too. This yields long jaw life. Combination vises are designed with maximum throat depth for greater clamping action to hold large parts. Forged steel, geared clamp bolt on swivel base maintains positive lock to avoid slippage under heavy pressure.

Catalog No.	Item Code	Throat Depth*		Jaw Width		Jaws Open <sup>Ω</sup>		Pipe Capacity	Weight	
NU.		in	mm	in	mm	in	mm	in-nom.	lbs	kg
2CA	01360	5 3/8	137	4 1/2	114	5	127	<sup>1</sup> /8 - 3 <sup>1</sup> / <sub>2</sub>	60.0	27.3







WHY REED?

Vises have enclosed screw assembly

for all-weather protection.





Only Reed has backed up its bench vises with a Lifetime Warranty for over 100+ years.



ΩSee illustration

<sup>\*\*3</sup> or more pieces in any combination must ship by truck freight.

ΩSee illustration

<sup>\*\*3</sup> or more pieces in any combination must ship by truck freight.