

1002 Series Couplings

Clay to CI, Plastic, Copper, Steel or Lead

* Insert bushing included

Red high torque clamps included

 new

18" x 18" (450 mm x 450 mm)	22.00 x 18.80 1002-1818	22.00 x 18.80 1002-1818RC*	21.90 x 19.00 5002-1818RC*
21" x 21" (525 mm x 525 mm)	24.30 x 22.30 1002-2121*	24.30 x 22.30 1002-2121RC*	
24" x 24" (600 mm x 600 mm)	29.00 x 25.00 1002-2424*	29.00 x 25.00 1002-2424RC*	
27" x 27" (700 mm x 700 mm)	32.40 x 28.25 1002-2727*		

1003 Series Couplings

Clay to AC or DI

NOMINAL PIPE SIZE	STANDARD	STRONG BACK 1000 RC SERIES	STRONG BACK 5000 RC SERIES	ECCENTRIC
4" x 4" (100 mm x 100 mm)	5.30 x 4.75 1003-44	5.30 x 4.85 1003-44RC*	5.30 x 4.85 5003-44RC*	
4" x 4" WC (100 mm x 100 mm)	5.60 x 4.95 1003-44WC	5.60 x 4.95 1003-44WCRC*		
4" x 6" (100 mm x 150 mm)	6.80 x 5.15 1003-46	6.95 x 5.15 1003-46RC*		
5" x 4" (125 mm x 100 mm)	6.05 x 4.95 1003-54*			
5" x 5" (125 mm x 100 mm)	6.00 x 5.85 1003-55			
6" x 4" (150 mm x 100 mm)	7.40 x 5.55 1003-64	7.50 x 5.00 1003-64RC*		7.50 x 5.00 1003-64EB
6" x 4" WC (150 mm x 100 mm)	8.00 x 5.00 1003-64WC*			
6" x 5" (150 mm x 125 mm)	7.50 x 7.50 1003-65*			
6" x 6" (150 mm x 150 mm)	7.25 x 6.90 1003-66	7.35 x 6.95 1003-66RC*	7.35 x 6.95 5003-66RC*	
6" x 6" WC (150 mm x 150 mm)	8.00 x 6.90 1003-66WC*	8.00 x 6.90 1003-66WCRC	8.00 x 6.90 5003-66WCRC*	
8" x 4" (200 mm x 100 mm)	9.65 x 4.95 1003-84*			
8" x 6" (200 mm x 150 mm)	9.65 x 7.20 1003-86*			
8" x 6" WC (200 mm x 150 mm)	9.95 x 7.20 1003-86WC*	10.00 x 7.10 1003-86WCRC*		
8" x 8" (200 mm x 200 mm)	9.50 x 9.00 1003-88	9.60 x 9.05 1003-88RC	9.60 x 9.05 5003-88RC*	
8" x 8" WC (200 mm x 200 mm)	10.00 x 8.95 1003-88WC*	10.00 x 8.95 1003-88WCRC*		
10" x 8" (250 mm x 200 mm)	12.50 x 9.05 1003-10-8*			12.50 x 9.05 1003-10-8EB
10" x 10" (250 mm x 250 mm)	12.50 x 11.10 1003-1010*	12.50 x 11.10 1003-1010RC*	12.50 x 11.10 5003-1010RC*	
10" x 10" WC (250 mm x 250 mm)	12.50 x 11.10 1003-1010WC*	12.50 x 11.10 1003-1010WCRC*		
12" x 10" (300 mm x 250 mm)	14.50 x 11.10 1003-1210*			
12" x 12" (300 mm x 300 mm)	14.65 x 13.25 1003-1212	14.50 x 13.20 1003-1212RC*	14.50 x 13.20 5003-1212RC	