Soil Pipe Cutters



NO. 286 SOIL PIPE CUTTER

- Articulating outward facing hooks simplifies connecting pipe.
- Adjusting knob for quickly adjusting the handles to the optimal cutting angle.
- Set the cutter once repeated cuts.

Catalog No.	Model No.	Deceription		Weight		
	Model No.	Description	lb.	kg		
59698	286	Soil Pipe Cutter	29	13.1		
33665	-	Chain Extension Assembly	1	0.5		
33670	-	Chain Assembly	-	-		



NO. 228 SOIL PIPE ASSEMBLY TOOL

- Handles all 1½" (40 mm) to 8" (200 mm) gasketed soil pipe without extra, loose attachments.
- Easy assembly of Y, tee and elbow fittings, as well as straight lengths from any angle.
- Slim, compact design lets one man assemble even large sizes quickly and easily.
- Removal of handle facilitates vertical and overhead pipe assembly.

Catalog No.	Model No.	Description	Capacity Capacity		Weight	
		Description	in.	mm	lb.	kg
32905	228	Soil Pipe Assembly Tool	1 ½ - 8	40 - 200	22 ¾	10.3



TORQUE WRENCHES

- Preset to eliminate guesswork in No Hub® soil pipe installations.
- Assures proper coupling tightness for strong, leak-free joints.
- No. 902 Torque Wrench The ⁵/₁₆" drive tightens with a fast ratchet action until the wrench clicks for accurate 68 inch-pounds +/- 8 inch-pounds torque.
- No. 904 Torque Wrench The ³/₈" drive tightens with a fast ratchet action until the wrench clicks for accurate 88 inch-pounds +/- 8 inch-pounds torque.

Catalog No.	Model No.	Description	Torque	Torque	Weight	
Gatalog No.	Model No. Description	in. lb.	NxM	lb.	kg	
31410	902	Torque Wrongh for No Hub Coot Iron Coil Dine Couplings	60	7	1/-	0.0
14988	904	Torque Wrench for No Hub Cast-Iron Soil Pipe Couplings	80	9	1/2	0.2

Power Threading Machines



Stand not included

MODEL 1224 THREADING MACHINE

The Model 1224 threads a wide range of pipe including black, galvanized and plastic-coated pipe, together with stainless steel, IMC and heavy-wall conduit, as well as rod up to 30 Rockwell C.

- An induction motor helps minimize noise.
- A special capacitor-start / capacitor-run motor allows the 1224 to thread a full range of material where voltage drop is experienced.
- $^{1}/_{4}$ "-2" Universal Die Head; 2 $^{1}/_{2}$ "-4" receding die head allows cutting of tapered or straight NPT/NPSM or BSPT/BSPP threads.
- · Constant and proper lubrication of dies and workpiece with throughhead oiling.

SPECIFICATIONS

- Nominal Pipe Capacity 1/4"-2" (6mm-100mm) @ 36 RPM, 2 ¹/₂"-4" (65mm-100mm) @ 12 RPM, 4"-6" (100mm-150mm) with 161 Geared Threader
- Bolt Capacity 1/4"-2" (6mm-50mm)
- Motor Control Reverse/off/forward, heavy-duty rotary-type and integral foot switch
- Gear Box Two-speed gear box with a 3:1 ratio
- Chuck Hammer-type with replaceable rocker-action jaw inserts
- Rear Centering Device Cam action
- Oiling Pump Self-priming, gerotor-type, automatic-reversing, constant-flow
- · Oiling Through die head

Catalog No.	Model No. Description Die	Die Head	e Head RPM		Frequency	Phase	e Motor	Amp Draw	Power	Wei	ght	
NO.				V	Hz		Type	Α	Power	lb.	kg	
26092		1/4" - 4" NPT Hammer Chuck Machine	711/714	36/12	120	60	1	Induction	151	1 ½ HP		
26097		74 - 4 NPT Halliller Gliuck Macilile	711/714	36/12	230	60	1	Induction	8	1 ½ HP	509	231
26127	1004		911/914	36/12	120	60	1	Induction	151	1 ½ HP		
26112		1/2-24 1/4" - 4" BSPT Hammer Chuck Machine	911/914	36/12	115	50	1	Induction	151	1700 W	463	210
26122			911/914	36/12	230	60	1	Induction	8	1700 W	509	231
29858*		1/4" - 4" NPT Hammer Chuck Machine	711/714	36/12	230	50 - 60	1	Induction	8	1700 W	463	210

^{*} Threading oil not included.

Standard Equipment

Catalog No. Model No.	Description	26092 1224	26097 1224	26127 1224	26112 1224	26122 1224	29858 1224
26132	Diehead, 711 SO Univ L/Dies	ı	ı				ı
26152	Diehead, 714 SO Recd L/Dies	ı	1				ı
26137	Diehead, 911 SO BSPT L/Dies			ı	ı	ı	ı
26147	Diehead, 913 QO BSPT L/Dies			ı	ı	ı	
26192	Dies. 1224 2-1/2"-4NPT HS	ı	ı				ı
47745	Dies, Univ 1/2-3/4 NPT	ı	1				ı
47750	Dies, Univ 1-2 NPT	ı	ı				ı
33642	Dies, 1224 2-1/2"-4 BSPT HS			ı	ı	ı	
66665	Dies, Univ 1-2 BSPT			ı	ı	ı	
66670	Dies, Univ 1/2-3/4 BSPT			1	ı	ı	
26212	1/4"-4" Wheel-Type Cutter	ı	ı		ı	ı	
26217	1/4"-4" Blade-Type Reamer	ı	ı	ı	ı	ı	ı
33125	Wheel, Cutter F229 3 & 4 HD	ı	ı	ı	ı	ı	ı

Catalog No. Model No.	Description	26092 1224	26097 1224	26127 1224	26112 1224	26122 1224	29858 1224
46030	Key, Hex 3/16	ı	ı	ı	ı	ı	ı
46040	Key, Hex 7/32	ı	ı	ı	- 1	1	1
46190	Key, Hex 1/4	ı	ı	ı	- 1	- 1	- 1
70835	Nu-Clear Oil	ı	I	ı			
	Wrench, 3/4 COMB	ı	ı	ı	ı	ı	
	Tool Box	ı	ı	ı	ı	ı	1
11931	Thread Cutting Oil						1
	Cutter, 764 ¹ /4-4" Pipe						I

