Tool Boxes



NO. 606 STANDARD SHAPE WITH TRAY

Heavy-duty tool boxes for tradesmen's use. Made of 18-gauge, cold-rolled prime steel. Two heavy-duty plated trunk-type catches. Plated top handle. Electrically welded construction. Continuous piano hinge. Durable baked red enamel finish, electrostatically sprayed.

Catalog No.	Model No.	Description	Length		Width		Height		Weight		Std.
			ft.	m	in.	mm	in.	mm	OZ.	g	Pack
33085	606	Standard Shape w/Tray	20	508	8 ½	216	9 ½	241	19 ½	8.8	1

Folding Rules



FIBERGLASS FOLDING RULES

Precision made of flexible heavy-duty fiberglass with embedded, easy-to-read boldface figures and graduations with red 16" stud marks and positive locking joints. Model 1602 is graduated on one side in millimeters with red markings every 10 cm. Reverse side reads in inches.

Catalog No.	Model No.	Description	Width		Length		Weight		Std.
Gatalog No.			in.	mm	ft.	m	OZ.	g	Pack
73365	1619	6' Outside Reading	5/8	16	6	1.8	7		6
73370	1619F	6' Inside Flat Reading*	5/8	16	6	1.8		100	6
73360	1620	6' Extension Rule	5/8	16	6	1.8	′	198	6
81280	1602	2m Metric Rule	5/8	16	7	2			6

^{*} Can be laid on floor to get true reading.





