

SeeSnake® Reels and Cameras – Compact Series

NEW
COMING IN 2019



SeeSnake Compact M40 with
docked CS6xPak



RIDGID® SEESNAKE COMPACT M40 WITH TRUSENSE™

The Compact M40 offers similar performance to the SeeSnake Mini in the popular Compact form-factor, combining a small package and all-in-one monitor capability (when used with the SeeSnake CS6xPak monitor). The Compact M40 features TruSense™ technology.



Best Use: The Compact M40 has 131' (40 m) of moderately stiff push cable, providing a good compromise between stiffness and the ability to navigate turns.

FEATURES

- Quick-release docking system for fast, efficient job setup with the SeeSnake CS6xPak monitor.
- Sturdy metal frame provides a solid base that makes it easy to push and retrieve the cable.
- Powerful Flexmitter® sonde has longer range and preserves the camera's ability to make turns.
- High dynamic range (HDR) image sensor offers bright, clear in-pipe imaging in difficult lighting conditions.
- TiltSense Sensor displays the camera's pitch in a pipe on a connected SeeSnake CSx series monitor.
- Included pipe guides center the camera for better in-pipe imaging.

SPECIFICATIONS

	SeeSnake Compact M40
Rated Pipe Capacity	1.5" to 8" (38 mm to 203 mm)
CABLE	
Max Cable Length	131.2' (40 m)
Minimum Bend Radius	3" (76 mm)
CAMERA	
Style	Self-Leveling TruSense
Diameter	1" (25 mm)
Length	1" (25 mm)
SONDE	
Frequency	512 Hz
Type	Flexmitter
DISTANCE MEASUREMENT	
Type	TruSense Counter
Data-Enabled	Two-Way

Catalog No.	Description	Weight	
		lb	kg
63818	SeeSnake Compact M40 System with 1 Battery and 1 Charger	31.5	14
63813	SeeSnake Compact M40 System	27.7	12.5
63673	SeeSnake Compact M40 (Reel Only)	22	9.9

Accessories

Catalog No.	Description
47793	36 mm Pipe Guide, 25 mm Camera, Pkg of 1
35338	45 mm Pipe Guide, 25mm Camera, Pkg of 2
97462	60 mm Pipe Guide, 25mm Camera, Pkg of 6
46708	85 mm Pipe Guide, 25mm Camera, Pkg of 2
46713	125 mm Pipe Guide, 25mm Camera, Pkg of 2
63868	Various Pipe Guides, 25mm Camera Head
17553	Spanner Wrench, 25 mm
56813	CS6xPak Digital Recording Monitor
57143	CS6xPak with 2 Batteries and 1 Charger
45363	AC Battery Adapter
44693	18 V Advanced Lithium 2.0 Ah Battery
44698	18 V Advanced Lithium 4.0 Ah Battery
43458	18 V Advanced Lithium Battery Charger

Replacement Parts

Catalog No.	Description
63853	25 mm Self-Leveling Camera Head - TruSense
63858	130' SeeSnake Compact M40 Push Cable
24703	Kickstand
33108	Interconnect Cable

SeeSnake® Reels and Cameras – Compact Series

NEW
COMING IN 2019



SeeSnake Compact C40
with docked CS6xPak



RIDGID® SEESNAKE COMPACT C40 WITH TRUSENSE™

The Compact C40 comes in the popular Compact form-factor, combining a small package and all-in-one monitor capability (when used with the SeeSnake CS6xPak monitor). The Compact C40 features TruSense™ technology.



Best Use: The Compact C40 has 131' (40 meters) of flexible push cable, providing good ability to fit in smaller diameter pipes and navigate turns.

FEATURES

- Quick-release docking system for fast, efficient job setup with the SeeSnake CS6xPak.
- Sturdy metal frame provides a solid base that makes it easy to push and retrieve the cable.
- Powerful FleXmitter® sonde has longer range and preserves the camera's ability to make turns.
- High dynamic range (HDR) image sensor offers bright, clear in-pipe imaging in difficult lighting conditions.
- TiltSense Sensor displays the camera's degree of a tilt on a connected SeeSnake CSx series monitor.
- Included pipe guides center the camera for better in-pipe imaging.

SPECIFICATIONS

SeeSnake Compact C40	
Rated Pipe Capacity	1.5" to 6" (38 mm to 152 mm)
CABLE	
Max Cable Length	131.2' (40 m)
Minimum Bend Radius	2.5" (64 mm)
CAMERA	
Style	Self-Leveling TruSense
Diameter	1" (25 mm)
Length	1" (25 mm)
SONDE	
Frequency	512 Hz
Type	FleXmitter
DISTANCE MEASUREMENT	
Type	Data-Enabled Integrated Counter
Data Communication	Two-Way

Catalog No.	Description	Weight	
		lb	kg
63828	SeeSnake Compact C40 System with 1 Battery and 1 Charger	27.1	12.3
63823	SeeSnake Compact C40 System	23.3	10.5
63668	SeeSnake Compact C40 (Reel Only)	17.6	8

Accessories

Catalog No.	Description
47793	36 mm Pipe Guide, 25 mm Camera, Pkg of 1
35338	45 mm Pipe Guide, 25 mm Camera, Pkg of 2
97462	60 mm Pipe Guide, 25 mm Camera, Pkg of 6
46708	85 mm Pipe Guide, 25 mm Camera, Pkg of 2
46713	125 mm Pipe Guide, 25 mm Camera, Pkg of 2
63868	Various Pipe Guides, 25 mm Camera Head
17553	Spanner Wrench, 25 mm
56813	CS6xPak Digital Recording Monitor
57143	CS6xPak with 2 Batteries and 1 Charger
45363	AC Battery Adapter
44693	18 V Advanced Lithium 2.0 Ah Battery
44698	18 V Advanced Lithium 4.0 Ah Battery
43458	18 V Advanced Lithium Battery Charger

Replacement Parts

Catalog No.	Description
63858	25 mm Self-Leveling Camera Head - TruSense
63863	130' SeeSnake Compact C40 Push Cable
24703	Kickstand
33108	Interconnect Cable