Sewer Sectional Machine Kit w/ CABLE DRIVE"

2871A-22, 2871-22

May Drain Line

Specifications:

Capacity	2" – 8" up to 200"
Cable Capacity	7/8" and 1/1-4"
Powered Cable Feed & Retract	Yes, CABLE DRIVE™
Cable Spin Speed	700 RPM
Height / Length	23" / 35"
Weight	74 lbs

Includes: 2871A-22 (7) 1-1/4" x 15' All Purpose Open Wind Cables, (2) Cable Containers, Straight Auger, Funnel Auger, Small Opening Tool, Medium Opening Tool, 3" Grease Cutter, 3" Root Cutter, 4" Root Cutter, Pin Key, Head Attachment Case;

All Kits Include: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Packs, Rear Guide Hose, Rapid Charger

Related Accessories:

47-53-2871 Cable Container;

47-53-2872 Rear Guide Hose;

48-53-2851 1-1/4" x 15' All Purpose Open Wind Sectional Cable; 48-53-2854 1-1/4" x 15' Heavy Duty Open Wind Sectional Cable;

48-53-2852 7/8" x 15' Open Wind Cable;

48-53-3830 Straight Auger for 7/8" Sectional Cable;

48-53-3831 Funnel Auger for 7/8" Sectional Cable; 48-53-3832 3" Root Cutter for 7/8" Sectional Cable;

48-53-3833 4" Root Cutter for 7/8" Sectional Cable;

48-53-3834 6" Root Cutter for 7/8" Sectional Cable;

48-53-3835 Small Opening Tool for 7/8" Sectional Cable;

48-53-3836 Medium Opening Tool for 7/8" Sectional Cable;

48-53-3837 3" Grease Cutter for 7/8" Sectional Cable;

48-53-3838 4" Grease Cutter for 7/8" Sectional Cable;

48-53-3840 Head Attachment Kit for 7/8" Sectional Cable;

48-53-4830 Straight Auger for 1-1/4" Sectional Cable; 48-53-4831 Funnel Auger for 1-1/4" Sectional Cable;

48-53-4832 3" Root Cutter for 1-1/4" Sectional Cable;

48-53-4833 4" Root Cutter for 1-1/4" Sectional Cable:

48-53-4834 6" Root Cutter for 1-1/4" Sectional Cable;

48-53-4835 Small Opening Tool for 1-1/4" Sectional Cable; 48-53-4836 Medium Opening Tool for 1-1/4" Sectional Cable;


48-53-4837 3" Grease Cutter for 1-1/4"" Sectional Cable;

48-53-4838 4" Grease Cutter for 1-1/4" Sectional Cable;

48-53-4840 Head Attachment Kit for 1-1/4" Sectional Cable:

44-60-0005 Pin Key for Drain Cleaning;

48-53-2839 Head Attachment Case



SWITCH PACK™ Sectional Drum System Kit

2775-211, 2775A-211, 2775B-211, 2775C-222, 2775E-211 Specifications:

Opcomoduonsi	
Maximum Drain Line Capacity	1-1/4" – 4" up to 100' (not for roots)
Drum Capacity	Inner Core Cables: 5/16" x 75', Best for 1-1/4" – 2-1/2" drain lines; 3/8" x 50', Best for 2" – 3" drain lines; 1/2" x 50', Best for 3" – 4" drain lines
	Open Wind Cables: 5/8" x 50', Best for 1-1/4" – 3" drain lines (soft blockages)
Backpack Straps	Yes
Removable Drum	Yes, Tool-Free
Cable Spin Speed	250 RPM
Electronic Foot Pedal	Yes
Integrated Drum Brake	Yes
Length	15.8"

Includes: 2775A-211: 5/16" x 75' Inner Core Drop Head Cable w/ RUST GUARD™ Plating:

2775B-211: 3/8" x 50' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key; 2775C-222: Additional M18™ REDLITHIUM™ XC5.0 Battery Pack, Additional

SWITCH PACK™ Drum w/ Anchor Cable, (2) 1/2" x 50' Inner Core Coupling Cables w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key;


2775E-211: 5/8" x 50' Open Wind Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1" Spade Bit, C-Cutter, Small Bulb Head, Small Drop Head), Pin Key;

All Kits Include: 2775-211: SWITCH PACK™ Powered Base, SWITCH PACK™ Drum w/ Anchor Cable, (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Multi-Voltage Charger

Related Accessory:

47-53-2775 SWITCH PACK™ Drum w/ Anchor Cable





Drain Cleaning Accessories

Compatible with MILWAUKEE® and other professional brand drain cleaning machines

RUST GUARD™ Plated Cables

48-53-2563 1/4" x 25' Inner Core Bulb Head Cable; 48-53-2564 1/4" x 25' Inner Core Drop Head Cable; 48-53-2671 1/4" x 35' Inner Core Bulb Head Cable; 48-53-2672 1/4" x 50' Inner Core Bulb Head Cable; 48-53-2561 5/16" x 25' Inner Core Bulb Head Cable; 48-53-2562 5/16" x 25' Inner Core Drop Head Cable; 48-53-2673 5/16" x 35' Inner Core Bulb Head Cable; 48-53-2674 5/16" x 50' Inner Core Bulb Head Cable; 48-53-2772 5/16" x 75' Inner Core Drop Head Cable; 48-53-2676 3/8" x 25' Inner Core Coupling Cable; 48-53-2675 3/8" x 35' Inner Core Coupling Cable; 48-53-2773 3/8" x 50' Inner Core Coupling Cable; 48-53-2774 1/2" x 50' Inner Core Coupling Cable;

RUST GUARD™ Plated Cable Attachments

Compatible with MILWAUKEE® Coupling Cables

48-53-2775 5/8" x 50' Open Wind Coupling Cable

48-53-2681 Small Bulb Head;

48-53-2682 Small Drop Head;

48-53-2683 1" Spade Bit:

48-53-2684 1" C-Cutter;

48-53-2685 5 Pc Small Cable Head Attachment Kit;

48-53-2786 Funnel Head; 48-53-2787 Medium Drop Head;

48-53-2788 1-1/2" Spade Bit;

48-53-2789 1-1/2" C-Cutter;

48-53-2790 5 Pc Medium Cable Head Attachment Kit

Drain Snake w/ CABLE DRIVE™ Locking Feed System Kit

2772A-21 (2772A-20 Tool-Only), 2772B-21XC

Specifications:

Maximum Drain Line Capacity	1-1/4" – 3" up to 50'
Drum Capacity	1/4" x 50', Best for 1-1/4" - 2" drain lines; 5/16" x 50', Best for 1-1/4" - 2-1/2" drain lines; 3/8" x 35', Best for 2" - 3" drain lines
Powered Cable Feed & Retract	Yes, CABLE DRIVE™
Variable Feed Speed	0 - 8" Per Second
Variable Spin Speed	0 – 600 RPM
Feed Lock	Yes, Twist Lock
Cable Lock	Yes, Twist Lock
LED Light	Yes
Length / Weight	19.5" / 8.2 lbs

Includes: 2772A-21 (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, 5/16" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating; **2772B-21XC** (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, 1/4" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating, 3/8" x 35' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Attachments (1" Spade Bit. 1" C-Cutter, Small Bulb Head, Small Drop Head), Pin Kev: 2772A-20 Only Includes 5/16" x 35' Inner Core Bulb Head Cable W RUST GUARD™ Plating, Battery and Charger Sold Separately; All Kits Include: Multi-Voltage Charger, Storage Bucket

M18™ Transfer Pump Kit

2771-21 (2771-20 Tool-Only)

Specifications:

Gallons Per Hour	480
Gallons Per Battery (XC3.0)	144
Maximum Lift	18'
Maximum Head Height	75'
Self-Priming	Yes
Flexible Impeller	Yes
Fittings	3/4" Brass Inlet and Outlet
Weight	7.5 lbs

Includes: (1) M18[™] REDLITHIUM[™] XC3.0 Battery Pack, (2) 3/4" Brass Fittings, Multi-Voltage Charger



