

M12™ Drain Snake Kit

2571-21 (2571-20 Tool-Only)

Specifications:

Max Drain Line Capacity	1-1/4" – 2-1/2", Up to 25'	
Drum Capacity	1/4" x 25', Best for 1-1/4" – 2" drain lines; 5/16" x 25', Best for 1-1/4" – 2-1/2" drain lines	
Variable Speed Spin	0 – 500 RPM	
LED Light	Yes	
Weight (without cable)	6.5 lbs	

Includes: (1) M12[™] REDLITHIUM[™] CP1.5 Battery Pack, 5/16" x 25' Inner Core Bulb Head Cable with Inner Drum, Charger, 5 Gallon Storage Bucket

Related Accessories:

48-53-2561 5/16" x 25' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating;

48-53-2562 5/16" x 25' Inner Core Drop Head Cable w/ RUST GUARD™ Plating;

48-53-2563 1/4" x 25' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating;

48-53-2564 1/4" x 25' Inner Core Drop Head Cable w/ RUST GUARD™ Plating



2572A-21, (2572A-20 Tool-Only), 2572B-21

Specifications:

Max Drain Line Capacity	1" – 4", Up to 35'
Variable Pressure	0 - 50 PSI
Variable Pressure Dial	Yes
LED Light	Yes
Length / Weight	20.8" / 7.5 lbs

2432-22XC, 2432-22 (2432-20 Tool-Only)

3/8" - 1"

Built-In

5.0 lbs

Includes: 2432-22XC (2) M12™ REDLITHIUM™ XC3.0 Battery Packs; **2432-22** (2) M12[™] REDLITHIUM[™]

All Kits Include: (3) ProPEX® Expansion Heads

(1/2", 3/4", 1"), Grease, Multi-Voltage Charger, Carrying Case

3/8" - 1" M12™ / Uponor

7.1" x 3.7" x 12.8"

Specifications:

Head Compatibility Dimensions (L x W x H)

CP1.5 Battery Packs

Related Accessories:

49-08-2400 ProPEX® Expander Cone Grease;

49-16-2403 3/8" ProPEX® Expansion Head;

49-16-2404 1/2" ProPEX® Expansion Head;

49-16-2405 5/8" ProPEX® Expansion Head;

49-16-2406 3/4" ProPEX® Expansion Head;

49-16-2408 1" ProPEX® Expansion Head

Capacity

Weight

Auto-Rotate

Includes: 2572A-21 (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Charger; 2572B-21 (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Charger, Toilet Seal Attachment, 10" Extension; All Kits Include: 2572A-20: 1" - 2" Drain Plug, 2" - 3" Drain Plug, 3" - 4" Drain Plug, Drain Shroud Attachment,

(3) Straight Connectors, 15° Offset Connector, Carrying Case



M12™ FORCE LOGIC™ **Press Tool Kit**

2473-22 (2473-20 No Jaw Kit)

Specifications:

	Capacity	1/2" - 1-1/4" CU
	Calibration Interval	32,000 Cycles (LED Indicator)
	Approximate Cycle Time	5 Seconds
	Press Force	5,400 lbs
	Length / Weight	12.8" / 3.8 lbs

Includes: 2473-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs, (3) Jaws (1/2", 3/4", 1"), Charger, Carrying Case; **2473-20** (2) M12™ REDLITHIUM™ CP1.5 Battery Packs, Charger, Carrying Case (No Jaws Included)

Related Accessories:

49-16-2450 M12[™] 1/2" Jaw; **49-16-2451** M12[™] 3/4" Jaw; **49-16-2452** M12[™] 1" Jaw: **49-16-2453** M12[™] 1-1/4" Jaw



M12™ No-Hub Driver Kit

2455-22 (2455-20 Tool-Only)

Specifications:

Torque Settings (3-Mode)	60 in-lbs / 80 in-lbs / Drill	1		
RPM	0 – 750			
Chuck Type	1/4" Hex			
Calibration Interval	25,000 Cycles (LED Indicator)			
Weight	2.7 lbs			

Includes: (2) M12[™] REDLITHIUM[™] CP1.5 Battery Packs, (3) SHOCKWAVE™ Nut Drivers (1/4", 5/16", 3/8"), Charger, Carrying Case

M12™ 10 oz Caulk & **Adhesive Gun Kit**

2441-21 (2441-20 Tool-Only)

Specifications:

Force	400 lbs
Inches Per Minute	0 - 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	4.1 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, 10 oz Carriage, M12™ 10 oz Plunger Rod and Piston Assembly, Charger

M12™ 20 oz Aluminum Barrel Sausage Style Caulk & Adhesive Gun Kit

Specifications:

	Force	400 lbs
	Inches Per Minute	0 – 29
	Speed Settings	6
	Auto-Reverse Anti-Drip	Yes
	Weight	4.9 lbs

Includes: (1) M12[™] REDLITHIUM[™] CP1.5 Battery Pack, 20 oz Aluminum Sausage Style Barrel, M12™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Charger

M12™ Quart Caulk & **Adhesive Gun Kit**

2444-21

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.5 lbs

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Quart Carriage, M12[™] Quart Plunger Rod and Piston Assembly, Charger

M12™ Caulk Gun Accessories

Compatible with 2441-21, 2442-21, 2444-21

31-12-0700 Caulk Gun Nozzle - Black;

48-08-0900 M12™ 10 oz Caulk and Adhesive Gun Conversion Kit;

48-08-0905 M12™ 20 oz Aluminum Barrel Sausage Style

Caulk and Adhesive Gun Conversion Kit;

48-08-0910 M12™ Quart Caulk and Adhesive Gun Conversion Kit:

48-08-1091 20 oz Aluminum Barrel Kit; 48-08-1096 20 oz Clear Barrel Kit



M12™ TRAPSNAKE™ 6¹ Toilet Auger Kit

2576-21 (2576-20 Tool-Only)

Specifications:

RPM	0 - 500	
Cable Lock	Yes	
Cable Size	6' x 1/2"	
Cable Head	Retriever Bulb	-
Replacement Cables	Available	-(
Moight	Q O lbc	- '

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Cable, Charger

Related Accessories:

48-53-2576 TRAPSNAKE™ 6' Toilet Auger Replacement Cable; 48-22-2576 TRAPSNAKE™ Toilet Auger Case

M12™ TRAPSNAKE™ 4¹ Urinal Auger Kit

2574-21 (2574-20 Tool-Only)

Specifications:

- poomoutione	
RPM	0 - 500
Cable Lock	Yes
Cable Size	4' x 3/8"
Cable Head	Bulb
Replacement Cables	Available
Weight	6.4 lbs



Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Cable, Charger

Related Accessories:

48-53-2577 TRAPSNAKE™ 4' Urinal Auger Replacement Cable; 48-22-2577 TRAPSNAKE™ Urinal Auger Case

