# M18 FUEL

1/4" Hex Impact Driver w/ ONE-KEY™ Kit

2857-22, 2857-22CT (2857-20 Tool-Only)

### Specifications:

Max Torque	2,000 in-lbs
IPM	0 – 4,300
RPM	0 – 3,600
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/4" Hex
Single Hand Bit Insertion	Yes
Length / Weight	4.6" / 3.8 lbs

Includes: 2857-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs: **2857-22CT** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs; All Kits Include: Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



## 1/4" Hex Impact Driver Kit

2853-22, 2853-22CT (2853-20 Tool-Only)

### **Specifications:**

Max Torque	2,000 in-lbs
IPM	0 – 4,300
RPM	0 – 3,600
DRIVE CONTROL™	4-Mode
Chuck Type	1/4" Hex
Single-Handed Bit Insertion	Yes
Length / Weight	4.6" / 3.8 lbs

**Includes: 2853-22** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> XC5.0 Battery Packs; 2853-22CT (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; All Kits Include: Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



## SURGE™ 1/4" Hex **Hydraulic Driver Kit**

2760-22, 2760-22CT (2760-20 Tool-Only)

## Specifications:

Specifications:	
Sustained Max Torque	450 in-lbs
IPM	0 – 4,000
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode
Length / Weight	5.0" / 3.9 lbs

Includes: 2760-22 (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> XC5.0 Battery Packs: **2760-22CT** (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; All Kits Include: Belt Clip, Bit Holder, Multi-Voltage Charger,

### M18™ Brushless 1/4" Hex **3-Speed Impact Driver**

2851-20 Tool-Only

### Specifications:

Max Torque	1,600 in-lbs
IPM	0 – 4,200
RPM	0 – 3,400
Chuck Type	1/4" Hex
DRIVE CONTROL™	3-Mode
Length / Weight	5.1" / 2.0 lbs

Battery and Charger Sold Separately

Includes: Belt Clip



## M18™ Compact Brushless 1/4" Hex Impact Driver Kit

2850-22CT (2850-20 Tool-Only)

### Specifications:

Max Torque	1,600 in-lbs
IPM	0 – 4,200
RPM	0 – 3,400
Chuck Type	1/4" Hex
Length / Weight	5.1" / 2.9 lbs

**Includes:** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case

## M18™ 1/4" Hex Compact **Impact Driver Kit**

2656-22CT (2656-20 Tool-Only)

## Specifications:

Max Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length / Weight	5.5" / 3.8 lbs

**Includes:** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



## M18™ 1/4" 2-Speed Impact Driver Kit

2657-22, 2657-22CT (2657-20 Tool-Only)

### Specifications:

-p	<del>-</del>
Max Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length / Weight	5.5" / 3.8 lbs

Includes: 2657-22 (2) M18™ REDLITHIUM™ XC3.0 Battery Packs; **2657-22CT** (2) M18™ REDLITHIUM™ CP1.5 Battery Packs: All Kits Include: Belt Clip, Multi-Voltage Charger, Carrying Case



### M18™ Right Angle **Impact Driver Kit**

### Specifications:

Max Torque (2-Mode)	350 / 675 in-lbs
IPM	0 - 2,400 / 0 - 3,400
RPM	0 - 1,500 / 0 - 2,250
Anvil Type	1/4" Hex
Length / Weight	14.1" / 3.9 lbs

Battery Packs; **2667-21CT** (1) M18™ REDLITHIUM™ CP1.5 Battery Pack;



Includes: 2667-22 (2) M18™ REDLITHIUM™ XC3.0 All Kits Include: Belt Clip, Multi-Voltage Charger, Carrying Case

# 

### **Drywall Screw Gun Kit** 2866-22, 2866-22CT (2866-20 Tool-Only)

### **Specifications:**

RPM	0 – 4,500	- 1
Belt Clip	Yes	ţ
Auto Start Mode	Yes	
Length / Weight	9.0" / 4.1 lbs	

**Includes: 2866-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs; **2866-22CT** (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; All Kits Include: Belt Clip, PR2 Bit, Multi-Voltage Charger, Contractor Bag

### Related Accessory:

49-20-0001 MILWAUKEE® Collated Magazine Screw Capacity: Up to 2" Compatible with all major screw brands

**Related Tool:** 

2627-22 M18™ Cut Out Tool Kit Pg. 48



## M18™ Right Angle **Impact Wrench Kit**

2668-22, 2668-21CT (2668-20 Tool-Only)

### Specifications:

Fastening Torque (2-Mode)	30 / 60 ft-lbs
Nut-Busting Torque	60 ft-lbs
IPM	0 - 2,400 / 0 - 3,400
RPM	0 - 1,500 / 0 - 2,250
Anvil Type	3/8"
Length / Weight	14.3" / 3.9 lbs

**Includes: 2668-22** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Packs; 2668-21CT (1) M18™ REDLITHIUM™ CP1.5 Battery Pack: All Kits Include: Belt Clip, Multi-Voltage Charger, Carrying Case

## 

### 1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™ Kit

2759-22, 2759B-22 (2759-20, 2759B-20 Tool-Only)

### Specifications:

Fastening Torque	220 ft-lbs
Nut-Busting Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode (Customizable)
Anvil Type	1/2" Pin Detent
Length / Weight	6.1" / 4.2 lbs

Includes: 2759-22 1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™; 2759B-22 1/2" Compact Impact Wrench w/ Friction Ring w/ ONE-KEY™; **All Kits Include:** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



## M18 FLEL

## 1/2" Compact Impact Wrench w/ Pin Detent Kit

2755-22, 2755B-22 (2755-20, 2755B-20 Tool-Only)

#### Specifications:

Fastening Torque	220 ft-lbs
Nut-Busting Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode
Anvil Type	1/2" Pin Detent
Length / Weight	6.1" / 4.2 lbs

Includes: 2755-22 1/2" Compact Impact Wrench w/ Pin Detent; 2755B-22 1/2" Compact Impact Wrench w/ Friction Ring; All Kits Include: (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case

### M18™ 1/2" Compact **Impact Wrench Kit**

2659-22 (2659-20 Tool-Only)

### Specifications:

	-
Fastening Torque	183 ft-lbs
Nut-Busting Torque	183 ft-lbs
IPM	0 – 3,350
RPM	0 – 2,450
Anvil Type	1/2" Pin Detent
Length / Weight	6.0" / 4.1 lbs

**Includes:** (2) M18<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case

