

M18[™] Search Light Kit

2354-21 (2354-20 Tool-Only) Specifications:

Lumens	1,250 / 1,200 / 600 / 1,200	
Modes	Spot/Flood, Flood, Spot, Strobe	
Beam Distance	730 yd / 668 m	
Water & Dust Rating	IP54	
Head Rotation	198°	
Length / Weight	11.5" / 3.1 lbs	

Includes: (1) M18[™] REDLITHIUM[™] XC5.0 Battery Pack, Shoulder Strap, Multi-Voltage Charger



M18[™] Utility Bucket Light Kit 2122-22HD, 2122-21HD (2122-20 Tool-Only) **Specifications:**

Lumens	2,500 / 2,200 / 800
Modes	Flood, Spot/Flood, Spot
Hands Free	Patented Spring Loaded Bucket Clamp
Water & Dust Rating	IP56
Length / Weight	13.8" / 8.3 lbs

Includes: 2122-22HD (2) M18[™] REDLITHIUM[™] HD9.0 Battery Packs; 2122-21HD (1) M18™ REDLITHIUM™ HD9 0 Battery Pack

All Kits Include: Rapid Charger, Storage Bag

M18[™] Work Light 2735-20 Tool-Only Specifications:

L	umens	100
ŀ	Hands Free	Integrated Hook
ŀ	lead Rotation	90°
Ba	attery and Charger	Sold Separately

M18[™] Compact Blower

Length / Weight 20.5" / 2.6 lbs

Battery and Charger Sold Separately

100 CFM

160 MPH

3-Speed Electronic

Includes: Flexible Nozzle, 9" Extension, Universal Inflator/Deflator

0884-20 Tool-Only

Max Air Volume

Max Air Speed

Switch

Specifications:



M18[™] Compact Vacuum 0882-20 Tool-Only ecifications

specification	15:	
Air Volume	40 CFM	
Inlet Diameter	1-1/4"	
Canister Volume	36 oz	
Filter	HEPA	
Weight	4.3 lbs	

Battery and Charger Sold Separately

Includes: 4' Flexible Hose, (2) Extension Tools, Crevice Tool, Floor Tool, Removable HEPA Filter

Related Accessory: 49-90-1951 HEPA Filter (2-F



Battery and Charger Sold Separately

Includes: HEPA Filter, 6' Flexible Hose, Crevice Tool, Utility Nozzle

Related Accessory: 49-90-1900 HEPA Filter

0886-20 Tool-Only

RPM (3 Settings)

Length / Weight

Max Air Flow

Specifications:



Battery and Charger Sold Separately

M18[™] Jobsite Fan

Includes: AC Adapter



🚯 🛛 Bluetooth

Specifications	51
Modes	Bluetooth® 4.2, AM/FM, AUX
Battery Charger	Charges all M18 [™] Batteries
Bluetooth® Range	100 ft
USB Charging Port	2.1A USB Charging Port for External Devices
Device Storage	Weather Sealed
Powered By	All M18 [™] Batteries, 120V AC

Battery Sold Separately

Includes: 3.2 mm Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)









M18 FUEL **3-in-1 Backpack Vacuum Kit** 0885-21HD (0885-20 Tool-Only) **Specifications:** Air Flow 55 CEM

AIr FIOW	55 CFIVI	
Suction (H ₂ O)	76"	
Air Watts	159	
Filter	HEPA	
Canister Volume	1 Gallon	
Material	Dry Material Pickup Only	
Weight	15.3 lbs	

Includes: (1) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC8.0 Battery Pack, Telescoping Extension Wand, Flexible Hose, HEPA Filter, Crevice Tool, Dust Extraction Adapter and Floor Tool, Rapid Charger

Related Accessories: 49-90-1963 HEPA Filter; 49-90-1964 9' Hose Accessory





LITHIUM

HEPA FILTER



M18[™] PACKOUT[™] **Radio + Charger** 2950-20 Tool-Only Creations

SYSTEM WIDE M18



HEPA

M18[™] Jobsite Radio/Charger

2792-20 Tool-Only Specifications:

•	
Modes	AM, FM, AUX, Bluetooth®
Battery Charger	Charges all M18 [™] Batteries
Bluetooth® Range	100 ft
USB Charging Port	2.1A USB Charging Port for External Devices
Device Storage	Weather Sealed Auxiliary Compartment
Powered By	All M18 [™] Batteries, 120V AC



Includes: 3.2 mm Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)











M18 [™] Jobsite Radio
2890-20 Tool-Only
Specifications:

Modes	AM, FM, AUX
USB Charging Port	2.1A USB Charging Port for External Devices
Device Storage	Weather Sealed Auxiliary Compartment
Powered By	All M18 [™] Batteries, 120V AC

Battery and Charger Sold Separately

Includes: 3.2 mm Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)





ଃ Bluetooth



M18[™] / M12[™] Wireless **Jobsite Speaker** 2891-20 Tool-Only **Encoifications**

Specifications:		
Modes	Bluetooth®, AUX (Cable Not Included)	
Bluetooth® Range	100 ft	
USB Charging Port	2.1A USB Charging Port for External Devices	
Powered By	All M18 [™] and M12 [™] Batteries, AC Adapter	

Battery and Charger Sold Separately Includes: AC Adapter



M18[™] Power Source 49-24-2371 Specifications:

USB Charging Port

Run-Time

Powered By

2.1A USB Charging Port for External Devices Up to 18 Hours All M18[™] Batteries



Battery Sold Separately

Powers all MILWAUKEE[®] M12[™] Heated Gear



