
OSHA

HEPA



HOLE HAWG® 1/2" Right Angle Drill Kit

2707-22HD, 2707-22 (2707-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	1/2" All Metal Chuck
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length / Weight	17.0" / 9.8 lbs

Includes: 2707-22HD (2) M18™ REDLITHIUM™ HD9.0

Battery Packs, Rapid Charger: 2707-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger All Kits Include: Chuck Key, Carrying Case

M18 FUEL HOLE HAWG® Right Angle Drill Kit w/ QUIK-LOK™

2708-22HD, 2708-22 (2708-20 Tool-Only) Specifications:

RPM	0 – 1,200
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length / Weight	17.0" / 9.3 lbs

Includes: 2708-22HD (2) M18[™] REDLITHIUM[™] HD9.0 Battery Packs, Rapid Charger; **2708-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger; All Kits Include: Carrying Case

M18 FUEL SUPER HAWG™ 1/2" **Right Angle Drill Kit** 2809-22 (2809-20 Tool-Only)

Specifications:

39

RPM	0 - 1,550	
Chuck Type	1/2" All Metal Chuck	
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6-1/4"	
Mechanical Clutch	In Low Speed	
Length / Weight	20 5" / 14 4 lbs	

Includes: (2) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC6.0 Battery Packs, Side Handle, Chuck Key, Rapid Charger, Contractor Bag

SUPER HAWG™ Right Angle Drill Kit w/ QUIK-LOK™ 2811-22 (2811-20 Tool-Only)

Specifications:

RPM	0 – 1,550	
Chuck Type	7/16" Hex QUIK-LOK™	
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6-1/4"	
Mechanical Clutch	In Low Speed	
Length / Weight	20.5" / 14.9 lbs	

Includes: (2) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC6.0 Battery Packs, Side Handle, Rapid Charger, Contractor Bag

M18 FUEL

1-1/2" Magnetic Drill Kit 2787-22HD

Specifications:

	Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
	RPM	400 / 690
	Magnet	Operates Without Electricity
	Dimensions (L x W x H)	13.8" x 7.5" x 15.5"
	Weight	30.5 lbs

Includes: (2) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC8.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, Rapid Charger, Carrying Case

1-1/2" Lineman **Magnetic Drill Kit**

2788-22HD

Specifications:

Capacity	1-1/2" Annular Gutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13.8" x 7.5" x 15.5"
Weight	30.4 lbs

Includes: (2) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC8.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, 12V Inverter, Rapid Charger, Carrying Case

1-3/4" SDS Max Rotary Hammer w/ ONE-KEY™ Kit 2718-22HD, 2718-21HD (2718-20 Tool-Only)

Specifications:

Impact Energy	8.1 ft-lbs
RPM	0 – 380
BPM	0 – 2,900
Clutch	AUTOSTOP™ E-Clutch
Vibration	10 m/s ²
2-Mode Operation	Rotary Hammer & Hammer Only
Weight	19.7 lbs



Includes: 2718-22HD (2) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Packs; **2718-21HD** (1) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack

All Kits Include: Side Handle, Grease Tube, Rapid Charger, Carrying Case

M18 FUEL 1-9/16" SDS Max **Rotary Hammer Kit** 2717-22HD (2717-20 Tool-Only)

Specifications:

=	•		
RPM	0 – 440		
BPM	0 – 3,000		REDLITHIUM
mpact Energy	5.0 ft-lbs		HIGH OUTPUT XC80
2-Mode Operation	Rotary Hammer	and Hamr	mer Only
Neight	13.8 lbs		

Related Accessory: 2306-22 M12™ HAMMERVAC™ Universal Dust Extractor

M18 FUEL 1-1/8" SDS Plus **Rotary Hammer Kit**

2715-22HD, 2715-22, 2715-22DE (2715-20 Tool-Only)

Specifications:

RPM	0 – 1,350
BPM	0 – 5,000
Impact Energy	3.3 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	10.1 lbs

Includes: 2715-22HD (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; 2715-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger; 2715-22DE (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger;

COMPLIANCE
OSHA
SOLUTION
CERTIFICATION
FILTER

All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ HAMMERVAC™ **Dedicated Dust Extractor**

2715-DE

Specifications:

Compatibility	For use with 2715-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"

Includes: Replacement Nozzle and HEPA Filter



Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Packs, Side Handle, Depth Rod, Rapid Charger, Carrying Case

Dedicated Dust Extractor 2712-DE Specifications:

Compatibility For use with 2712-20 Engineered to Fit in the Most In-Line **Dedicated Design** Confined Workspaces Adjustable Easily and Precisely Adjust Depth Stop and Ruler for Accurate Hole Depths Replaceable Filters 99.97% of Debris

M18™ HAMMERVAC™

5/8" Includes: Replacement Nozzle and HEPA Filter

0.3 Microns and Above

M18 FLEL

Certified HEPA Filter

Max Bit Size

1" SDS Plus D-Handle **Rotary Hammer Kit**

2713-22HD, 2713-22 (2713-20 Tool-Only)

Specifications:

Capacity	1"
Impact Energy	2.15 ft-lbs
RPM	0 – 1,500
BPM	0 - 4,400
Length / Weight	16.5" / 8.5 lbs

Includes: 2713-22HD (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; 2713-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger;

All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ 7/8" SDS Plus **Rotary Hammer Kit**

2605-22 (2605-20 Tool-Only)

Specifications:

RPM	0 - 1,400
BPM	0 – 4,800
Impact Energy	1.4 ft-lbs
3-Mode Operation	Hammer Only, R

Rotary Hammer and Rotation Only 7.2 lbs Weight

Includes: (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

Related Accessory: 2306-22 M12™ HAMMERVAC™ Universal Dust Extractor

M18 FLEL 1" SDS Plus **Rotary Hammer Kit**

2712-22, 2712-22DE (2712-20 Tool-Only)

Specifications:

RPIVI	0 - 1,400
BPM	0 – 4,900
Impact Energy	1.7 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	9.4 lbs

Includes: 2712-22 (2) M18[™] REDLITHIUM[™] XC5.0 Battery Packs, Multi-Voltage Charger; **2712-22DE** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger;

All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ 5/8" SDS Plus **Rotary Hammer Kit** 2612-22, 2612-21 (2612-20 Tool-Only)

Specifications:

0 - 1,300

BPM	0 – 7,000
Impact Energy	1.0 ft-lbs
2-Mode Operation	Rotary Hammer and Rotation Only
Weight	5.5 lbs

Includes: 2612-22 (2) M18[™] REDLITHIUM[™] XC3.0 Battery Packs; 2612-21 (1) M18™ REDLITHIUM™ XC3.0

All Kits Include: Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

Related Accessory: 2306-22 M12™ HAMMERVAC™ Universal Dust Extractor