

ECON-O-GRIP®

PETRO ECON-O-GRIP®



Econ-O-Grip® Plug Features:

- Cost effective method for plugging open-ended pipe
- Works well as a pipe dust cover

Equipped with:

- Galvanized metal plates and bolts
- Natural rubber O-ring

Petro Econ-O-Grip® Plug Features:

- Cost effective, chemical-resistant plug
- Works well as a pipe dust cover

Equipped with:

- Stainless-steel bolt and plate
- Chemical resistant nitrile rubber

ECONO-O-GRIP



| PART NUMBER | NOMINAL SIZE | USAGE RANGE | MAXIMUM BACK PRESSURE | | LENGTH | PRODUCT WEIGHT | |
|-------------|-----------------|----------------------------|-----------------------|------|------------------|------------------|-----------------------|
| | | | psi | bar | | | |
| 271519 | 1.5" (40 mm) | 1.44"–1.65" (37–42 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.56" (65 mm) | 3.5 oz (0.1 kg) |
| 271527 | 2" (50 mm) | 1.96"–2.25" (50–57 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.62" (67 mm) | 5 oz (0.14 kg) |
| 271535 | 3" (75 mm) | 2.86"–3.25" (73–82 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.64" (67 mm) | 8.5 oz (0.24 kg) |
| 271543 | 4" (100 mm) | 3.78"–4.5" (96–114 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 3.25" (82 mm) | 12.48 oz (0.35 kg) |
| 271551 | 5" (125 mm) | 4.62"–5.3" (117–135 mm) | 1 | 0,07 | 2 ft. (0.7 M) | 3.55" (90 mm) | 1.1 lbs (0.5 kg) |
| 271578 | 6" (150 mm) | 5.62"–6.4" (143–162 mm) | 1 | 0,07 | 2 ft. (0.7 M) | 3.19" (81 mm) | 1.6 lbs (0.7 kg) |

PETRO ECONO-O-GRIP



| PART NUMBER | NOMINAL SIZE | USAGE RANGE | MAXIMUM BACK PRESSURE | | LENGTH | PRODUCT WEIGHT | |
|-------------|-----------------|----------------------------|-----------------------|------|------------------|------------------|-----------------------|
| | | | psi | bar | | | |
| 273318 | 1.5" (40 mm) | 1.44"–1.65" (37–42 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.56" (65 mm) | 3.5 oz (0.1 kg) |
| 273328 | 2" (50 mm) | 1.96"–2.25" (50–57 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.62" (67 mm) | 5 oz (0.14 kg) |
| 273338 | 3" (75 mm) | 2.86"–3.25" (73–82 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 2.64" (67 mm) | 8.5 oz (0.24 kg) |
| 273348 | 4" (100 mm) | 3.78"–4.3" (96–109 mm) | 2 | 0,14 | 5 ft. (1.4 M) | 3.25" (82 mm) | 12.48 oz (0.35 kg) |
| 273358 | 5" (125 mm) | 4.62"–5.3" (117–135 mm) | 1 | 0,07 | 2 ft. (0.7 M) | 3.55" (90 mm) | 1.1 lbs (0.5 kg) |
| 273368 | 6" (150 mm) | 5.62"–6.4" (143–162 mm) | 1 | 0,07 | 2 ft. (0.7 M) | 3.19" (81 mm) | 1.6 lbs (0.7 kg) |

ALWAYS BLOCK PLUGS WHEN CONDUCTING AIR TESTS.