

POLY-LIFT LINES



Hi-Flow Poly Lift Line:

- Greater Lifting Strength
- Recommended for plugs 6" to 48"
- Retard gauge: helps prevent "peg-out" damage
- Heavy-duty rubber gauge cover protects gauge
- 3/8" heavy-duty ID hose for quick inflate/deflate
- Quick-dump valve for easy deflation
- Industrial Quick Disconnect
- Designed for use with plugs with removable inflator valve

Super-Flow Hose with Gauge:

- Designed for large diameter multi-size plugs - (24"–48" to 54"–96")
- 3/4" Heavy-duty hose for both durability and faster deflation
- Retard gauge: Helps prevent gauge "peg-out"
- Heavy-duty rubber gauge cover protects gauge
- Utilizes traditional "crow's foot" air compressor fittings
- Quick dump valve for easy deflation

Poly-Lift Line:

- Great for plugs up to 15"
- 3/16" ID hose
- Threaded connection fittings

HI-FLOW HOSE



| PART NUMBER | LENGTH |
|-------------|---------------------------------|
| 383108 | Hi-Flow Hose, 10 FT W/Gauge |
| 383208 | Hi-Flow Hose, 20 FT W/Gauge |
| 383308 | Hi-Flow Hose, 30 FT W/Gauge |
| 383408 | Hi-Flow Hose, 40 FT W/Gauge |
| 383508 | Hi-Flow Hose, 50' with gauge |
| 380108 | Hi-Flow Hose, 10' without gauge |
| 380208 | Hi-Flow Hose, 20' without gauge |
| 380308 | Hi-Flow Hose, 30' without gauge |
| 380408 | Hi-Flow Hose, 40' without gauge |
| 380508 | Hi-Flow Hose, 50' without gauge |

Consult factory for lines without gauges.

SUPER-FLOW HOSE WITH GAUGE



| PART NUMBER | DESCRIPTION |
|-------------|--------------------------------|
| 341208 | Super-Flow Hose, 20 FT W/Gauge |
| 341308 | Super-Flow Hose, 30 FT W/Gauge |
| 341408 | Super-Flow Hose, 40 FT W/Gauge |

POLY-LIFT LINE



| PART NUMBER | PRODUCT LENGTH |
|-------------|----------------|
| 261076 | 10' |
| 261084 | 20' |
| 261106 | 30' |
| 261114 | 40' |