

Plain Hose Nozzles

Features:

- finish: satin
- maximum operating pressure: **100 PSI** (water only) at **70°F (21°C)**

Size	Thread	Overall Length	Orifice	Replacement Gasket	Brass	
					Previous Part #	Part #
3/4"	GHT	6"	1/4"	<b>KRW5</b>	500SN6	<b>BN6</b>
3/4"	NPSH	6"	1/4"	<b>KRW5</b>	---	<b>BN7</b>
1"	NPSH	8"	5/16"	<b>KRW10</b>	---	<b>BN10</b>
1 1/4"	NPSH	10"	3/8"	<b>KRW15</b>	---	<b>BN12</b>
1 1/2"	NPSH	10"	1/2"	<b>KRW20</b>	---	<b>BN15</b>
2"	NPSH	12"	9/16"	<b>SW200</b>	---	<b>BN20</b>
2 1/2"	NPSH	12"	1"	<b>KRW35</b>	---	<b>BN25</b>
1"	NST (NH)	8"	5/16"	<b>SW100F</b>	---	<b>BN10F</b>
1 1/2"	NST (NH)	10"	1/2"	<b>SW150</b>	---	<b>BN15F</b>
2 1/2"	NST (NH)	12"	1"	<b>SW250</b>	---	<b>BN25F</b>
1 1/2"	NYFD	10"	1/2"	<b>SW150</b>	---	<b>BN15NYFD</b>
2 1/2"	NYFD	12"	1"	<b>SW250</b>	---	<b>BN25NYFD</b>



Industrial Washdown Nozzles

Features:

- maximum operating pressure: **100 PSI** (water only) at **70°F (21°C)**
- delivers 30° - 60° - 90° fog pattern
- shut off - straight stream - fog
- supplied with bumper

Size	Thread	90° Spray GPM @ 100 PSI	Brass Part #
1 1/2"	NPSH	88 (+/-12)	<b>WDN150</b>
	NST (NH)	88 (+/-12)	<b>WDN150NST</b>




Swivel Connectors for Washdown Spray Guns

Ball Type Swivel x Hose Shank

Features:

- swivel connector for stainless spray nozzles
- 360° ball type swivel adapter helps prevent hose kinking

NPT	Hose ID	Brass Part #	300 Stainless Steel Part #
1/2"	1/2"	---	<b>SSA44</b>
	5/8"	---	<b>SSA54</b>
	3/4"	---	<b>SSA64</b>
3/8"	1/2"	<b>BSA34</b>	---



Straight Swivel x Hose Shank

Features:

- swivel body
- gasket: EPDM

NPT	Hose ID	Brass Part #	Stainless Steel Part #
1/2"	1/2"	<b>BNS44</b>	<b>BNS44SS</b>
	3/4"	<b>BNS64</b>	<b>BNS64SS</b>



Straight Swivel x GHT Thread

NPT	Female GHT	Brass Part #
1/2"	3/4"	<b>BMAS974</b>

