

### Type C Couplers coupler x hose shank

**Features:**

- supplied with EPDM gaskets, 304 stainless steel handles and pins
- maximum operating pressure: **125 PSI** (½" - 1"), **100 PSI** (1¼" - 2"), **60 PSI** (3") and **50 PSI** (4"); recommendations based on the use of mating Dixon® fittings at an ambient temperature of **70°F (21°C)** with standard seal installed
- ½" couplers and adapters will interchange with ¾" couplers and adapters, only the threads and barbs are ½"
- 1¼" couplers and adapters will interchange with 1½" couplers and adapters, only the threads and barbs are 1¼"
- replacements: gasket use EPR on page 168, pull rings use **R200SS** on page 171, safety clip use **GSAFETYCLIP** on page 182
- NOT recommended for use with PTFE gaskets. Polypropylene cam and groove should not be mixed with metal fittings. 



Size	Glass-Filled Polypropylene Part #	Optional Qty
¾" x ½"	<b>PPC50</b>	24
¾"	<b>PPC75</b>	24
1"	<b>PPC100</b>	24
1½" x 1¼"	<b>PPC125</b>	24
1½"	<b>PPC150</b>	24
2"	<b>PPC200</b>	24
3"	<b>PPC300</b>	24
4"	<b>PPC400</b> <sup>1</sup>	8

<sup>1</sup> 4" coupler has 4 handles

### Type D Couplers coupler x female NPT

**Features:**

- supplied with EPDM gaskets, 304 stainless steel handles and pins
- maximum operating pressure: **125 PSI** (½" - 1"), **100 PSI** (1¼" - 2"), **60 PSI** (3") and **50 PSI** (4"); recommendations based on the use of mating Dixon® fittings at an ambient temperature of **70°F (21°C)** with standard seal installed
- ½" couplers and adapters will interchange with ¾" couplers and adapters, only the threads and barbs are ½"
- 1¼" couplers and adapters will interchange with 1½" couplers and adapters, only the threads and barbs are 1¼"
- replacements: gasket use EPR on page 168, pull rings use **R200SS** on page 171, safety clip use **GSAFETYCLIP** on page 182
- NOT recommended for use with PTFE gaskets. Polypropylene cam and groove should not be mixed with metal fittings. 



Size	Glass-Filled Polypropylene Part #	Optional Qty
¾" x ½"	<b>PPD50</b>	24
¾"	<b>PPD75</b>	24
1"	<b>PPD100</b>	24
1½" x 1¼"	<b>PPD125</b>	24
1½"	<b>PPD150</b>	24
2"	<b>PPD200</b>	24
3"	<b>PPD300</b>	24
4"	<b>PPD400</b> <sup>1</sup>	8

<sup>1</sup> 4" coupler has 4 handles