

18V XR XRP 3 SPEED PREMIUM COMBI DRILL

DCD996P2

Max. Torque	95Nm
No Load Speed	0 - 450/1300/2000rpm
No Load Speed (Hammer)	0 - 500/1500/2250rpm
Beats Per Minute	0 - 8600/25500/38250bpm
Max. Drilling Capacity Wood	55mm
Max. Drilling Capacity Metal	15mm
Max. Drilling Capacity Masonry	13mm



DCD997P2B-GB - 5AH TOOLCONNECT BLUETOOTH BATTERIES

18V XR XRP 3 SPEED COMBI DRILL

DCD985M2

Max. Torque	80Nm
No Load Speed	0 - 575/1350/2000rpm
Beats Per Minute	9775/22900bpm
Max. Drilling Capacity Wood	50mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	16mm



18V XR 2 SPEED COMPACT COMBI DRILL

DCD796P2

Max. Torque	70Nm
No Load Speed	0 - 550/2000rpm
Beats Per Minute	0 - 9350/34000bpm
Max. Drilling Capacity Wood	40mm
Max. Drilling Capacity Metal	13mm
Max. Drilling Capacity Masonry	13mm




DCD796D2 - 2AH BATTERIES DCD797D2B - 2AH TOOLCONNECT BLUETOOTH BATTERIES

18V XR XRP 3 SPEED PREMIUM DRILL DRIVER

DCD991P2


Max. Torque	95Nm
No Load Speed	0 - 450/1300/2000rpm
No Load Speed (Hammer Mode)	0 - 500/1500/2250rpm
Max. Drilling Capacity Wood	55mm
Max. Drilling Capacity Metal	15mm



18V XR 2 SPEED COMPACT DRILL DRIVER

DCD791P2

Max. Torque	70Nm
No Load Speed	0 - 550/2000rpm
Max. Drilling Capacity Wood	40mm
Max. Drilling Capacity Metal	13mm



18V XR 3 SPEED IMPACT DRIVER

DCF887P2

Max. Torque	205Nm
No Load Speed	0 - 1000/2800/3250rpm
Impacts Per Minute	0 - 3800ipm
Bit Holder	1/4" (6.35mm)
Max. Bolt Diameter	M12



DCF887D2 - 2AH BATTERIES DCF887N - BARE UNIT