NAILERS

GUARANTEED TOUGH:









20V MAX* XR Lithium Ion **Brushless Framing Nailer Kit** 20V MAX* XR Brushless **Framing Nailer** (Tool Only)

18V XRPTM 1-1/4" - 2-1/2" (31.7 mm - 63.5 mm) 15 Gauge 34° Angled Finish Nailer Kit

| SPECIFICATIONS | DCN692M1 | DCN692B | DC628K |
|------------------------|---|---------------------|---|
| Volts | 20V MAX* | 20V MAX* | 18V |
| Operating Mode | Bump & Sequential | Bump & Sequential | Bump & Sequential |
| Nailing Rate | 2 nails/sec | 2 nails/sec | 4-5 nails/sec |
| Nail Diameter/Type | .113131 gauge | .113131 gauge | 15 ga. DA type gauge |
| Mag. Angle/Capacity | 33°/ 55 nails | 33°/55 nails | 34°/ 110 nails |
| Nail Length Capacity | 2" - 3-1/2" | 2" - 3-1/2" | 1-1/4" - 2-1/2" |
| Magazine Loading | Lock & Load | Lock & Load | Rear - load |
| Integrated Belt Hook | Yes | Yes | Yes |
| Tool-Free Jam Cleaning | No | No | Yes |
| Tool-Free Depth Adj. | Yes | Yes | Yes |
| Weight | 9.1 lbs | 7.7 lbs (tool only) | 8.9 lbs |
| Charger/Batteries | Fast Charger / (1) 20V MAX* XR Lithium Ion (4.0 Ah) | Sold Separately | 1-Hour Charger / (1) 18V XRPTM |
| Includes | No-mar tip | - | No-mar tip, reversible belt hook, DEWALT safety glasses |















18V XRPTM 1-1/4" - 2-1/2" (31.7 mm - 63.5 mm) 16 Gauge 20° Angled Finish Nailer Kit

18V XRPTM 1-1/4" - 2-1/2" (31.7 mm - 63.5 mm) 16 Gauge Straight Finish Nailer Kit

18V XRPTM 5/8" - 2" (15.8 mm - 50.8 mm) 18 Gauge Straight Brad Nailer Kit

(15.8 mm - 50.8 mm) 18 Gauge Straight Brad Nailer (Tool Only)

| SPECIFICATIONS | DC618K | DC616K | DC608K | DC608B |
|------------------------|---|---|---|---|
| Volts | 18V | 18V | 18V | 18V |
| Operating Mode | Bump & Sequential | Bump & Sequential | Bump & Sequential | Bump & Sequential |
| Nailing Rate | 4-5 nails/sec | 4-5 nails/sec | 4-5 nails/sec | 4-5 nails/sec |
| Nail Diameter/Type | 16 gauge | 16 gauge | 18 gauge | 18 gauge |
| Mag. Angle/Capacity | 20°/ 110 nails | Straight/ 110 nails | Straight/ 110 nails | Straight/ 110 nails |
| Nail Length Capacity | 1-1/4" - 2-1/2" | 1-1/4" - 2-1/2" | 5/8" - 2" | 5/8" - 2" |
| Magazine Loading | Rear - load | Rear - load | Side - load | Side - load |
| Integrated Belt Hook | Yes | Yes | Yes | Yes |
| Tool-Free Jam Cleaning | Yes | Yes | Yes | Yes |
| Tool-Free Depth Adj. | Yes | Yes | Yes | Yes |
| Weight | 8.5 lbs | 8.5 lbs | 7.4 lbs | 7.4 lbs (tool only) |
| Charger/Batteries | 1-Hour Charger / (1) 18V XRP™ | 1-Hour Charger / (1) 18V XRP™ | 1-Hour Charger / (1) 18V XRPTM | Sold Separately |
| Includes | No-mar tip, reversible belt hook, DEWALT safety glasses | No-mar tip, reversible belt hook, DEWALT safety glasses | Reversible belt hook, DEWALT safety glasses | Reversible belt hook, DEWALT safety glasses |

| SHEARS | 18V 18 Gauge Off-Set Shear (Tool Only) | 18V 18 Gauge Swivel Head and Shear | 18V 18 Gauge Swivel Head and Shear (Tool Only) |
|---------------------|---|------------------------------------|---|
| SPECIFICATIONS | DC495B | DC490KA | DC490B |
| Volts | 18V | 18V | 18V |
| Stroke/Min | 0-2,300 spm | 0-2,300 spm | 0-2,300 spm |
| Min. Cutting Radius | 1" | 5.5" | 5.5" |
| Capacity in Steel | 18 Gauge | 18 Gauge | 18 Gauge |
| Weight | 3.7 lbs (tool only) | 6.1 lbs | 3.7 lbs (tool only) |
| Charger/Batteries | Sold Separately | 1-Hour Charger / (2) 18V XRP™ | Sold Separately |

| Volts | 18V | 18V | 18V |
|---------------------|---------------------|-------------------------------|---------------------|
| Stroke/Min | 0-2,300 spm | 0-2,300 spm | 0-2,300 spm |
| Min. Cutting Radius | 1" | 5.5" | 5.5" |
| Capacity in Steel | 18 Gauge | 18 Gauge | 18 Gauge |
| Weight | 3.7 lbs (tool only) | 6.1 lbs | 3.7 lbs (tool only) |
| Charger/Batteries | Sold Separately | 1-Hour Charger / (2) 18V XRP™ | Sold Separately |
| Includes | Blade wrench | Blade wrench | Blade wrench |
| | | <u> </u> | |







and 4-1/2" cutting wheel









20V MAX* 4-1/4" (114 mm) Cut-Off Tool (Tool Only)

20V MAX* Lithium Ion (114 mm) Cut-Off Tool Kit 4-1/4" (114 mm) Cut-Off Tool Kit

| SPECIFICATIONS | DC415KL | DCG412M2 | DCG412B |
|-------------------|---|---|---|
| Volts | 36V | 20V MAX* | 20V MAX* |
| No Load Speed | 6,500 rpm | 6,500 rpm | 6,500 rpm |
| Spindle Lock | Yes | Yes | Yes |
| Spindle Thread | 5/8" - 11 | 5/8" | 5/8" |
| Weight | 7.2 lbs | 6.5 lbs | 5.1 lbs (tool only) |
| Charger/Batteries | 1-Hour Charger / (2) 36V Lithium Ion | Fast Charger / (2) 20V MAX* XR Lithium Ion (4.0 Ah) | Sold Separately |
| Includes | Type 1 guards, Type 27 guard, Wrench, (2) matched flanges, 2-position side handle | Type 1 guards, Wrench and 2-position side handle | Type 1 guards, Wrench, and 2-position side handle |

(continued on next page)