

CROSS LINE LASER

DW089K

Beam Colour	Red
Accuracy	+/-3mm @ 10m
Self-levelling Range	+/-4°
Max. Working Range with Detector	50m
IP Rating	54
Number Of Beams	3 - Horizontal, Vertical, Side
Tripod Connection	5/8"
Laser Class	2
Modes Control	3 beams Separately 1 Horizontal, 2 Vertical, Cross line & 90° s²
Power Source	4AA



RED LINE LASER DETECTOR

DE0892

Compatibility	DW088, DW089
Max. Working Range	50m
Power Source	1 x 9V



GREEN LINE LASER DETECTOR

DE0892G

Compatibility	DW088CG, DCE088D1G, DCE089D1G, DCE0825D1G
Max. Working Range	50m
Power Source	1 x 9V



WATERPROOF DIGITAL ROTARY LASER DETECTOR

DE0772

Compatibility	DCE074D1R
Working Range	Rotary > 300m (Radius)
Power Source	1 x 9V
Adjustable Volume Control	Up to 100dBA



3 SPOT LASER

DW083K

Beam Colour	Red
Accuracy	+/-2mm @ 10m
Self-levelling Range	+/-4°
IP Rating	54
Number Of Beams	3 - Horizontal, 2 Vertical (Up & Down)
Indoor Visibility Range	30m
Tripod Connection	1/4"
Laser Class	2
Power Source	4 x AA



30M LASER DISTANCE MEASURE

DW033

Levelling Accuracy	+/-3mm @ 10m
Max. Working Range	30m
Laser Class	2
Power Source	2 x AAA

