


C14 Electric Hand Held Saw



Part # 5801601, Cat # 48975

**LIGHT WEIGHT
& POWERFUL**



- | | |
|-----------------------|--------------------------|
| 1. Dust Port | 4. Magnesium Blade Guard |
| 2. LED Overload Light | 5. Water Feed System |
| 3. Guide Rollers | |

14" Blade Capacity

Features & Benefits:

- Wet or dry cutting
- Overload protection with load warning LED light - visible to operator
- Electrical cord with PRCD protection
- Detachable guide rollers
- Splash guard to protect from water spray
- Handles designed for optimal control
- Tool-free blade guard angle adjustment
- Lightweight magnesium blade guard
- Externally accessible motor brushes
- Standard water feed system with fine adjustable flow and quick release coupling and durable hose

Specifications:

Power Input:	15A / 20A
Voltage:	120V / 110V
Minimum RPM:	4500
Arbor:	1"
Max. Cutting Depth:	5"
Cut Direction:	Down
Weight:	17 lbs. (18 lbs. with guide rollers)

Diamond Products Limited
333 Prospect St. Elyria, OH 44035
800-321-5336 · www.diamondproducts.com

