

### Red Handles for Use with Acetylene



AA-1



GG-4

### ACET-O-LITE "Screw-in Style"

Part No. AA-1

Adjustment valve in the front for single hand operation. Needle valve design enables very fine flame adjustments. *This torch will keep your tips burning efficiently in drafts, winds, and adverse conditions.* It is made with quality brass, has a durable handle and uses standard 3/8-24 LH "A" size hose fittings. Seat gasket, RUB-100. **Goss Acet-O-Lite torch handle will work with all "BA" style tips listed on page 7.**

### TARGET TORCH "Snap-in Style"

Part No. GG-4

This handle has a quick disconnect fitting to rapidly change tips. Tips are designed to operate efficiently in winds and adverse conditions. Comfortable grooved handle is made of very durable materials. Uses 3/8-24 LH "A" hose fittings.

**Goss Target Torch handle will work with all "GA" style tips listed on page 8.**

### SPECIALTY TIPS "Snap-in Style"

SNAP-IN design used with GG-4 handle. Duel feather flame design for special applications.

#### SPLIT-FIRE TIP



GA-GT

TIP NUMBER	FLAME DIAMETER	SOFT SOLDER	SILVER SILVER BRAZE
GA-GT	(2) 1/4"	3/4"	3/4"
GA-3J	5/16"	1/4" to 1"	1/8" to 1/2"
GA-8J	3/8"	1" to 2"	1/2" to 1"

 **COLOR-CODED "O" RINGS**  
Red for Acetylene (RUB-136R)

### "Snap-in Style"

The J-Tip design allows you to solder or braze in hard-to-reach areas while safely pointing the flame away from flammable surfaces.

#### J-TIPS



GA-3J



GA-8J


### ACETYLENE REGULATORS

These UL LISTED regulators, manufactured from solid brass, are made for rugged use. *They have a specially designed conical seat and diaphragm.* The inlets have filters to prevent dirt from entering the regulator.

**EA-1G** B cyl. connection; "A" Hose fitting 3/8 - 24 L.H.

**EA-2G** MC cyl. connection; "A" Hose fitting 3/8 - 24 L.H.

**GAUGE ONLY**  
Part No.  
MA-80-16



### ACETYLENE HOSE

Hose assemblies are made of quality 7/16" OD x 3/16" ID single ply fabric reinforced Grade R hose.

*It has a 200 PSI working pressure.*

**HA3-6** Hose 6 feet long with "A" (3/8 - 24) connections

**HA3-12** Hose 12 feet long with "A" (3/8 - 24) connections

**HA3-25** Hose 25 feet long with "A" (3/8 - 24) connections

