

PRODUCT DATA SHEET AEC PREMIER STRAW[®] DOUBLE NET

DESCRIPTION

AEC Premier Straw Double Net erosion control blanket (ECB) consists of the finest available agricultural straw with 75% four-inch fibers or greater fiber length, and it is certified weed seed free. The straw fibers are evenly distributed throughout the entire area of the blanket. The top and bottom of each blanket is covered with degradable polypropylene netting. AEC Premier Straw Double Net shall be manufactured in the U.S.A.

AEC Premier Straw Double Net has a design soil loss ratio (event-based RUSLE C factor) of .05 and is typically suitable for slopes up to 2H:1V. AEC Premier Straw Double Net is rated for channel flows up to 7.0 ft/s (2.1 m/s) and 1.75 lb/ft² (84 Pa) shear stress.

PHYSICAL PROPERTIES

AEC Premier Straw Double Net measurements at time of manufacturing:

Width	8.0 ft (2.4 m)	16.0 ft (4.9 m)
Length	112.5 ft (34.3 m)	112.5 ft (34.3 m)
Area	$100.0 \text{ yd}^2 (83.6 \text{ m}^2)$	$200.0 \text{ yd}^2 (167.2 \text{ m}^2)$
Weight ^a	50.0 lb (22.7 kg)	100 lb (45.4 kg)
Mass per Unit Area	0.50lb/yd^2	0.50lb/yd^2
(± 10%)	(0.27 kg/m^2)	(0.27 kg/m^2)
Net Openings	0.50 in x 0.50 in (12.7 mm x 12.7 mm)	0.50 in x 0.50 in (12.7 mm x 12.7 mm)

TYPICAL INDEX VALUES

Index Property	Test Method	Value
Thickness	ASTM D 6525	0.31 in (7.9 mm)
Light Penetration	ASTM D 6567	26.4%
Resiliency	ASTM D 6524	61%
Mass per Unit Area	ASTM D 6475	$0.43 \text{ lb/yd}^2 (0.233 \text{ kg/m}^2)$
MD-Tensile Strength Max.	ASTM D 6818	196.8 lb/ft (2.87 kN/m)
TD-Tensile Strength Max.	ASTM D 6818	92.4 lb/ft (1.35 kN/m)
MD-Elongation	ASTM D 6818	32.7%
TD-Elongation	ASTM D 6818	26.4%
Swell	ECTC Procedure	22%
Water Absorption	ASTM D 1117/ECTC	460%
Bench-Scale Rain Splash	ASTM D 7101	$SLR = 9.58 @ 2 in/hr_{1}^{b,c}$
Bench-Scale Rain Splash	ASTM D 7101	$SLR = 7.53 @ 4 in/hr_{1}^{b,c}$
Bench-Scale Rain Splash	ASTM D 7101	$SLR = 5.92 @ 6 in/hr^{b,c}$
Bench-Scale Shear	ASTM D 7207	$1.95 \text{ lb/ft}^2 @ 0.5 \text{ in soil loss}^{\circ}$
Germination Improvement	ASTM D 7322	530%
Bench-Scale Rain Splash Bench-Scale Shear	ASTM D 7101 ASTM D 7207	SLR = 9.58 @ 2 in/hr b,cSLR = 7.53 @ 4 in/hr b,cSLR = 5.92 @ 6 in/hr b,c1.95 lb/ft2 @ 0.5 in soil loss c530%

^a Weight is based on a dry fiber weight basis at time of manufacture. Baseline moisture content of AEC Premier Straw fibers is 15%.

^b SLR is the Soil Loss Ratio, as reported by NTPEP/AASHTO. ^c Bench-scale index values should not be used for design purposes.

