ProTalk has the right radio for every work environment's.



ProTalk

PKT-23K TK-3230DX

Improve store security, enhance the customer experience and improve profits.

- 4-channel PKT-23 with 1.5 Watts. More power equals more coverage.
- Excellent voice quality even in noisy environments.
- Super compact clip to a lanyard, slip it in a pocket.
- Ideal for retail, hospitality, restaurants and service industries.



ProTalk

NX-P500/TK-2400V16P/3400U16P NX-240V16P2/TK-340U16P2

Coordinate materials and personnel for quick response and increased safety.

- Mil-spec tough analog and digital models.
- Powerful 2-Watts for long range or on-site
- Built for construction, manufacturing, warehouses and industry.
- Submersible up to 1 hour.



ProTalk

TK-2402V16P/3402U16P NX-240V16P/340U16P TK-2360ISV16P/3360ISU16P

Increase safety and work productivity by responding quickly to changing needs.

- Enhanced digital for 20% more coverage.
- Meets tough mil-spec standards with intrinsically safe models.
- Loud, clear, world-renowned KENWOOD audio in loud settings.
- Designed for factories, plants and heavy industry.



















Why ProTalk?

Durability

- Meets or exceeds military standards: MIL-STD 810 C, D, E, F & G, including "driven rain" and IP54/55 dust and water intrusion.
- Perfect for demanding work settings and any weather: Unique sealed case and metal diecast chassis.
- Optimum radio integrity: Belt clip integrated into the chassis.
- Removable Antennas: Rapid swap-out to different models.
- Commercial grade radios: Built to the highest KENWOOD quality standards.

Sophisticated Features

- Wireless cloning is standard: Fast and easy cloning of other radios within range.
- Lightweight, high capacity batteries: Last up to 18 hours, charge in only 3 hours.
- Compatible with comparable BRS and LMR radios: Easy integration.
- Extend range with repeaters and talk to other higher tier digital radios: ProTalk expands your capabilities.
- On the go USB charging: Never be with out a charged radio.

Choice

- Select the right radio now: Based on the coverage and features you need.
- **Compact PKT-23:** Weighs less than a deck of cards and smaller than a credit card.
- Affordable digital NX-240V/340U: Extend your coverage.
- Intrinsically safe TK-2360ISV16P/TK-3360ISU16P: Use where combustible materials are present.
- Industry leading 2 or 3 year warranties: 2yr 3yr We back up ProTalk quality.



ProTalk® Business Two-Way Radios

ProTalk LT PKT-23 UHF Radio





The PKT-23 LT is the smallest and lightest UHF two-way radio from KENWOOD at only 3.9oz. Easy to handle and operate, this 1.5 Watt, 4 channel transceiver packs a solid punch that fits in your pocket and is smaller that a credit card.

- 1.5 Watts Transmit Power
- 8 Channels
- 39-QT/168-DQT Coded Squelch
- Super Lock (Manager Key Lock)
- Scan Function
- 2 PF Keys
- Enhanced Kenwood Audio
- VOX Ready
- Voice Announcement
- Bell Tone Alert

- LED Battery Status Indicator
- 1,430 mAh Li-lon battery with up to 15 hours of talk time *(5-5-90) and 3 hours fast charger
- IP54 & MIL-STD 810 C/D/E/F/G 11 items
- Battery Saver
- Time Out Timer
- Monitor
- Wireless Cloning
- 2 year Radio Warranty



ACCESSORIES INCLUDED

- Li-lon Rechargeable Battery
- Spring Action Belt Clip
- Fast Charging Cup
- Fixed Antenna
- Owner's Manual
- 2-Year Warranty

For a full list of optional accessories, please visit the KENWOOD website.



^{*5-5-90 - 5%} Transmit, 5% Receive and 90% Standby