



T5632-W

3.6A USB Type-A/Type-A Wall Outlet Charger with 15A Tamper-Resistant Receptacles

Combination Duplex Receptacle/Outlet and USB Charger. 15 Amp, 125 Volt, Decora Tamper-Resistant Receptacle/Outlet, NEMA 5-15R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - White

- SMART - Built-in smart chip recognizes the individual device's charging

requirement to optimize the charge

- POWERFUL Two high-powered charging ports with 3.6A of charging power
- CONVENIENT No more searching for charging adapters! Upgrade your existing

outlets so you can charge up to two USB powered electronics at once, leaving the outlets free for additional power needs

 EASY - Compact design fits in a standard wallbox and works with Decora and Decora Plus screwless wallplates.

Technical Information

Product Features

Amperage : 15 ABrand : DecoraGrade : Residential/CommercialSpecification GradeGrounding : GroundingHorsepower Rating : 15A-1/2 HPNEMA : 5-15RProduct Type : Outlet/USB ComboRatings : 15A-125VType : Type A/A Duplex ReceptacleVoltage : 125 VACWallplate : Not Included

Electrical Specifications Amperage : 15 A Flammability : Rated V-0 per UL 94 Grounding : Grounding Horsepower Rating : 15A-1/2 HP Operating Temperature : -10°C to 40°C

Ratings: 15A-125V

Environmental Specifications Body Material : Thermoplastic Color : White Cover Material : Thermoplastic Flammability : Rated V-0 per UL 94 Operating Temperature : -10°C to 40°C Strap Material : Steel Material Specifications Body Material : Thermoplastic Color : White Cover Material : Thermoplastic Product ID : Stamped on Strap Strap Material : Steel Terminal Accom. : 14-12 AWG Terminal ID : Brass-Hot Black-Hot White-Neutral Green-Gnd Termination : Back & Side Torque Range : 12-14 inch pounds

Mechanical Specifications

Amperage : 15 A Color : White Grade : Residential/Commercial Specification Grade Product ID : Stamped on Strap Terminal Accom. : 14-12 AWG Terminal ID : Brass-Hot Black-Hot White-Neutral Green-Gnd Termination : Back & Side

Torque Range : 12-14 inch pounds

Standards and Certifications

FCC Part 15 : Class B Listed : cCSAus NOM : 057 UL 1310 : Yes UL 498 : Yes Warranty : 5-Year Limited

Features and Benefits

- Perfect for use in residential applications such as kitchens, bedrooms and home

offices and in commercial applications such as hotels, airports, restaurants and

cafes, salons, office cubicles and college dorm rooms

- Smart chip recognizes and optimizes the charging requirements of individual devices
- Tested to withstand over 10,000 insertions.
- Compatible with USB 3.1, 3.0, 2.0, 1.1 devices
- Fits in a standard wallbox, is compatible with standard wallplates and can be multi-ganged with other devices
- Easy to install. Can replace existing outlets
- No data transfer capability
- Compatible with Decora® wallplates and Decora Plus[™] screwless wallplates. Wallplate sold separately

Patents*

*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747 Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 · FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

