

SUBMERSIBLE CLEAN WATER PUMPS

Features

- 1.25" to 6" diameter discharge
- Selected models UL and CUL listed
- Compact and streamlined design with thermal overload protection
- Single-phase and three-phase motors available
- Double oil-filled seal provides positive lubrication (selected models)



Technical specifications

MODEL	DISCHARGE IN (MM)	GPM (LPM)	TOTAL HEAD FT (M)	VOLTAGE PHASE	HP (KW) ¹	DIAMETER IN (MM)	WEIGHT LBS (KG)
YELLSUB	1.25 (38)	33 (125)	15 (4.6)	115 1Ø	0.25 (0.185)	5.3 (136)	6(2.72)
SS233	2 (50)	60 (227)	20 (6.1)	115 1Ø	0.5 (0.37)	8.1 (206)	15.5(7)
ST2038P	2 (50)	60 (227)	38 (11.5)	115 1Ø	1.0 (0.75)	7.7 (196)	31(14)
ST2037	2 (50)	73 (276)	37 (11.3)	115 1Ø	1.0 (0.75)	7.4 (188)	31(14)
ST2037F #	2 (50)	73 (276)	37 (11.3)	115 1Ø	1.0 (0.75)	7.4 (188)	31(14)
ST2047	2 (50)	87 (329)	47 (14.3)	115 1Ø	1.0 (0.74)	7.4 (188)	33(15)
ST3020BCUL	3 (75)	170 (644)	72 (22)	230 1Ø	2.0 (1.5)	6.7 (170)	67(30)
ST3050D*†	3 (75)	264 (999)	86 (26)	230/460 3Ø	5.0 (3.7)	10.2 (259)	120(54)
ST41230*†	4 (101)	423 (1,601)	138 (42)	230 3Ø	10 (7.4)	12.5 (318)	205(93)
ST41460*†	4 (101)	423 (1,601)	138 (42)	460 3Ø	10 (7.4)	12.5 (318)	205(93)
ST61230*†	6 (152)	674 (2,423)	105 (32)	230 3Ø	15 (11.1)	14 (356)	301(136)
ST61460*†	6 (152)	674 (2,423)	105 (32)	460 3Ø	15 (11.1)	14 (356)	301(136)

* Three-phase—specify voltage when ordering
Models ST3050D, ST41230, ST41460, ST61230, ST1460
require a Control Box when ordering

¹ See page 50 for details.

† Not currently available for sale or use in Canada

SUBMERSIBLE TRASH PUMPS

Features

- Compact design with thermal-overload protection
- Handles solids up to 1" in diameter
- PX400 designed with plastic/stainless steel housing



Technical specifications

MODEL	DISCHARGE IN (MM)	GPM (LPM)	MAX HEAD FT (M)	VOLTAGE PHASE	HP (KW) ¹	DIAMETER IN (MM)	WEIGHT LBS (KG)
PX400 ¹	2 (51)	72 (273)	34 (10.3)	115 1Ø	0.5 (0.37)	10 (254)	25 (11)
ST2040T	2 (51)	79 (299)	40 (12.2)	115 1Ø	1.0 (0.75)	10.3 (267)	34 (15.4)
ST2040TF #	2 (51)	79 (299)	40 (12.2)	115 1Ø	1.0 (0.75)	10.3 (267)	34 (15.4)
ST2010TCUL	2 (51)	95 (360)	45 (13.7)	115 1Ø	1.0 (0.75)	10.3 (267)	77 (35)

¹ See page 50 for details.

with integrated Float Switch