

Project Name

Location

Prepared By



SATCO S9211

9.8A19/OMNI/LED/5000K

Notes

General

Status	Discontinued
Watts	9.8
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	900
Beam Spread	300
Dimmable	Yes Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---

Physical

MOL	4.5
MOD	2.38

Additional Information

Warranty	3 Year Limited
----------	----------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
RoHS Compliant	Yes
SDS Sheet	LED_Lamp