



### FEATURES

- Energy Savings of up to 85%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Alabaster Glass with Steel Trim in Oil-Rubbed Bronze Finish
- Die Formed of 22 Gauge Plated Steel
- Replaces 2 x 60W Incandescent
- Dimmable

### APPLICATIONS

- Hallways
- Bedrooms
- Lobbies

### CERTIFICATIONS

- UL/cUL Listed
- Energy Star

### SPECIFICATIONS

Part Number: **LED1101-34-2CCT**

**Limited Manufacturer Warranty:** 3 Years  
**Kelvin Temperature (CCT):** 3000K or 4000K  
**Wattage:** 18.43  
**Lumens:** 1,106  
**Efficacy:** 60.01 lm/w  
**CRI:** 80  
**Dimmable:** 0-10V Dimming  
**Input Voltage:** DC 120V

**Certifications:** UL Listed  
**DLC Listed:** No  
**Average Hour Life:** 50,000 hrs  
**Max. Ambient Temperature:** 45°C  
**Min. Ambient Temperature:** -20°C  
**Power Factor:** >0.9  
**THD:** <20%

### TECHNICAL

**Weight:** 2.68 lbs  
**Length:** 11.5"  
**Product Height:** 3.5"

**Product Width:** 11.5"  
**LED Beam Angel:** 120  
**LED Type:** Integrated LED Array





Project:  Date:   
Prepared by:   
Comments:

LINE DRAWINGS

