

Culpepper Series



Two-Piece Skirted Toilet

Product Features

- Available in dual flush (1.1/1.6 gpf), UHET (1.0 gpf) & HET (1.28 gpf) or low consumption (1.6 gpf)
- Elongated bowl
- 16-1/2" bowl height
- Two-piece vitreous china
- 2" fully glazed trapway
- 7" x 6" water surface
- Anti-siphon fill valve
- Gravity fed, box rim
- Close coupled tank with cover
- Quick connect, 2 bolt tank to bowl installation
- White only
- 2" flush valve
- Sanitary bar
- Seat and supply not included
- EPA WaterSense compliant when used with a 1.28 gpf or less tank
- Meets ANSI ASME A112.19.2-2013-CSA_B45.-13



PF9002SWH / PF5112NHEWH

Model Numbers

PF9002SWH	1.1-1.6 gpf elongated skirted bowl White
PF5112WHM	1.6 gpf tank with color match flush lever
PF5112HEWH	1.28 gpf tank with color match flush lever
PF5112NHEWH	1.28 gpf tank with chrome flush lever
PF9312WH	1.1/1.6 gpf dual flush tank with color match flush lever
PF9312PWH	1.1/1.6 gpf dual flush tank with chrome push button
PF2312WH	1.0 gpf tank with color match flush lever

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO fixtures carry a lifetime limited warranty on the vitreous china and a 5-year limited warranty on the fittings. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless we agree in writing to do otherwise.



Two-Piece Skirted Toilet

Certifications

Meets strict flushing performance guidelines established by the EPA (Environmental Protection Agency) WaterSense program. Leadership in Energy and Environmental Design (LEED) Compliant. Los Angeles Department of Water and Power (LADWP) Compliant.

Model Number	A	B	C	D	E	F	R
PF5112WHM/ PF9002SWH	31-1/4" (793mm)	15-3/4" (400mm)	18-1/2" (470mm)	8-1/2" (216mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)
PF5112HEWH/ PF9002SWH	31-1/4" (793mm)	15-3/4" (400mm)	18-1/2" (470mm)	8-1/2" (216mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)
PF5112NHEWH/ PF9002SWH	31-1/4" (793mm)	31-1/4" (793mm)	18-1/2" (470mm)	8" (202mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)
PF9312WH/ PF9002SWH	31-1/4" (793mm)	15-3/4" (400mm)	18-1/2" (470mm)	8-1/2" (216mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)
PF9312PWH/ PF9002SWH	31-1/4" (793mm)	15-3/4" (400mm)	18-1/2" (470mm)	8-1/2" (216mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)
PF2312WH/ PF9002SWH	31-1/4" (793mm)	15-3/4" (400mm)	18-1/2" (470mm)	8-1/2" (216mm)	16-1/4" (413mm)	30-1/2" (775mm)	12" (305mm)

