


Type _____

P84-AT

Catalog No.	Lamping	Dimensions (Inches)		
		A	B	C
P84-AT	See Trim Specifications	7-7/8	10-3/4	5-1/2
		Ceiling Opening 5-1/4		



Specifications:

Wiring

- Universal J-box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Integral knock out free Romex clamps
- 1/2" & 3/4" knock outs for rigid conduit or BX fittings

Construction

- Shallow housing for 2X6 construction
- Notched housing for chalkline alignment
- Overspray protection
- Socket can be used as a temporary work light with an 'A' lamp
- Porcelain socket with nickel-plated brass screw shell
- Housing adjusts from 1/2" to 1-1/2" thick ceilings
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)

Bar Hangers

- Integral nailers for wood joist construction
- Integral T-bar mounting clamps
- Inter-connected to securely span 24" spacing
- Lock to secure housing
- Captive
- 90-degree mounting for tight spaces

Labeling

- IC and Non-IC rated
- UL-CUL Listed for damp location and through branch wiring
- Complies with Washington State Energy Code (WSEC) requirement for air-tight

Lamp/Trim

- Socket mounts to trim for optimum performance and consistent lamp position
- Positive upward spring action forces trim to fit snugly against the ceiling