

# FANNING

## FILTRATION KITCHEN FAUCET

SKU: 949181



### CONTENTS

FAUCET .....	PAGE 2
FAUCET WITH DECKPLATE .....	PAGE 3

### FEATURES


- Installation Type: Single-hole
- Faucet Holes: 1
- Hand Sprayer Material: ABS
- Handle Type: Lever
- Design: Modern
- Faucet Material: Brass
- Swivel Spout: Yes
- Ceramic Disk Cartridges: Yes
- Hot and Cold Indicators: No
- Drain included: No
- Maximum Flow Rate:
  - 1.8 gpm (6.8 L/m) @ 60 psi
- Maximum Filtered Flow Rate:
  - 0.8 gpm (3.01 L/m) @ 60 psi
- Included Deck Plate Can be Used to Hide Unused Mounting Holes
- Handle Material: Metal
- Single Hole or 3-hole Sink Installation
- Optional Deck Plate Included
- 2 Function Spray Head: Stream and Spray
- Features GE Dual Flow Filtration System
- Separated Waterways, No Cross Connection
  - Between Filtered and Tap Water
- LED Indicator For Filter Replacement
- Filter Warranty: Limited 30-Day Manufacturer's
- Filter Life: 6 Months or 300 Gallons

REVISED 07/17/2020

# FANNING

## FILTRATION KITCHEN FAUCET

SKU: 949181



### FEATURES

Length: 5"  
 Width: 10-1/4"  
 Height: 20-1/4"  
 Height to Spout: 9-7/8"  
 Spout Reach: 8-1/2"  
 Base Plate Length: 2-1/2"  
 Base Plate Width: 2-1/2"  
 Handle Length: 3-1/4"  
 Height to Bottom of Handle: 4-7/8"  
 IPS: 1/2"

### CODES/STANDARDS

cUPC  
 ASME A112.18.1/CSA B125.1  
 ICC/ANSI A117.1 (when installed according to ADA standards)  
 NSF/ANSI 61  
 NSF/ANSI 372  
 CEC Listed  
 CalGreen  
 Massachusetts Accepted



### PRODUCT IMAGE



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

PAGE 2  
Code: SHXCFA101

## SKU: 949181

