

SINGLE-HOLE GOOSENECK BATHROOM FAUCET

SKU: 948580



FEATURES

Design: Modern

Drain is only compatible with sinks that have an overflow.

SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.


CONTENTS

FAUCET PAGE 2

REVISED 07/30/2020

SINGLE-HOLE GOOSENECK BATHROOM FAUCET

SKU: 948580



FEATURES

Installation Type: Single-Hole
 Max. Countertop Thickness: 2-1/4"
 Faucet Centers: Single-Hole
 Handle Type: Lever
 Faucet Material: Brass
 Length: 4"
 Width: 6-3/8"
 Height: 7"
 Height To Spout: 5"
 Spout Reach: 5-1/4"
 Base Plate Length: 2-1/8"
 Base Plate Width: 2-1/8"
 Handle Length: 3"
 Height to Bottom of Handle: 2-3/8"
 Ceramic Disc Cartridges: Yes
 Hot and Cold Indicators: No
 IPS: 1/2"
 Drain Included: Yes
 Overflow Hole: Yes
 Fits Drain Hole Size: 1-1/2"
 Maximum Flow Rate: 1.2 gpm (gallons per minute)

CODES/STANDARDS

cUPC
 ASME A112.18.1/CSA B125.1
 NSF/ANSI 61
 NSF/ANSI 372
 ICC/ANSI A117.1 (when installed according to ADA standards)
 WaterSense
 CEC Listed
 CALGreen
 Massachusetts Accepted



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

Code: SHWSCRI100BN, SHWSCRI100CP