



## Core Fixed Rail CRRF Series

### Features

This decorative dimmable fixed rail features reliable high-performance LEDs. Heads swivel and pivot to direct light where needed and remains cool to the touch when lit. Applications that this fixture could fit well include: kitchens, retail environments, and anywhere that needs highlighted illumination. The fixture mounts to a standard junction box (not included). These fixtures mount to the ceiling or wall.

### Construction

The canopy is 22-gauge stamped steel and the rail is made of 20-gauge steel tube. Power supply connections must be made inside a junction box (not included).

### Finish

The canopy, rail, and individual rail heads are plated in a polished chrome or satin nickel finish with a clear lacquer topcoat.

### Diffuser

Frosted acrylic.

### Electrical

Direct wired with a constant current low voltage electric LED driver rated at 120 VAC. Dimmable with standard 2-wire (TRIAC) or electronic low voltage (ELV) dimmer switch.

### Lamping

Unit is supplied with rail heads. Each rail head contains non-replaceable high power LEDs which produce a total of 400 lumens per head. The LEDs have an average life of 50,000 hours. 3000K. 90 CRI.

### Certification

All fixtures are cETLus listed for damp locations.  
ENERGY STAR qualified  
Title 24/JA8 compliant.

### Warranty




Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

**Specifications and dimensions**  
subject to change without notice.

## Ordering Information:

Polished Chrome	Satin Nickel	Qty.	Source Lumens	L	W	H
CRRF4400L30PC	CRRF4400L30SN	25W	1600	36-3/8"	5-3/8"	6-1/4"
	CRRF6400L30SN	42W	2400	55-1/8"	5-1/4"	7-1/2"

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		



Product can be dimmed down to 10% of full scale using a standard two-wire dimmer.

Brand	Series	Model#
Lutron®	Diva	DVELV-300P
	Maestro	MAELV-600P
	Skylark	SELV-300P