



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Armitage Pendant AGP Series

Features

Clear or tinted glass pendant is suspended with a 9 ft. adjustable cord and can be ordered individual or with a multipoint canopy. Fixture mounts to a standard junction box (not included).

Construction

The glass cylinder is 8" tall and 10" in diameter and held together into place by stem and top cap. The canopy fits over a standard junction box. Power supply connections must be made inside a junction box (not included).

Finish

The canopy is plated in satin nickel.

Diffuser

Glass cylinder pendant is .40" thick. Glass colors include aqua (AQ), clear (CL), clear crackle (CC), and brown (BR).

Electrical

Input 120 VAC / 60 Hz.

Lamping

1 x 60 watt (MAX) medium base bulb (not included).


Certification

All fixtures are cULus listed for indoor damp locations.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.


Specifications and dimensions
subject to change without notice.



Ordering Information:

	Clear Crackle	Brown	Clear	Aqua	Qty.	Lamp	Pendant DIA.	H
Monopoint	AGPI0MBSNCC	AGPI0MBSNBR	AGPI0MBSNCL	AGPI0MBSNAQ	1	60W (MAX)*	10"	8"
3-Light Linear	AGPI0MBSNCCCLR3	AGPI0MBSNBRLNR3	AGPI0MBSNCLLR3	AGPI0MBSNAQLNR3	3	60W (MAX)*	10"	8"
3-Light Round	AGPI0MBSNCCRND3	AGPI0MBSNBRRND3	AGPI0MBSNCLRND3	AGPI0MBSNAQRND3	3	60W (MAX)*	10"	8"

*Sockets can be labeled for reduced wattage upon request.



3-Light Linear Canopy
41" L x 5" W x 1-1/2" D



3-Light Round Canopy
15-1/8" DIA. x 1-3/8" H