

Model 108 Chlorinator/Dechlorinator

<i>ITEM</i>	<i>PART NUMBER</i>
Model 108 Chlorinator/Dechlorinator	108

MODEL 108 CHLORINATOR/DECHLORINATOR

Capable of disinfecting flows up to 10,000 gpd, a 4 1/2" diameter inlet; lockable; optional risers are available. The maximum flow rate is 35 gpm (gallons per minute).

FEATURES

- **MOUNTING** - Equipped with a mounting base for easy installation in a chlorine contact chamber. For installation on discharge lines, a 4 1/2" inside diameter inlet and outlet are provided.
- **MATERIALS** - Each are constructed with high density polyethylene, which is chemical and ultraviolet resistant.
- **FEED TUBES** - 2 removable PVC tubes, 28" long and 3" inside diameter, with caps. Each tube holds 34 tablets. *It is not recommended filling the tubes to the top.
- **OUTLET WEIR PLATE** - A permanently affixed, outlet weir plate is included to regulate effluent level.
- **INLET Baffle** - An inlet baffle plate to control the direction and velocity of flow within the tablet feeder is supplied.
- **RISERS (OPTIONAL)** - For expanding tablet feeder to grade on deep installations.
- **LOCKABLE COVER** - Can be locked to prevent unauthorized access.
- **LIMITED WARRANTY** - Every tablet feeder carries a 10-year limited warranty against defective material and workmanship.

