



SnakeBite™

LOCKING CONNECTOR

APPLICATION

Use to securely connect up to three wires. Gauge specific (10, 12, 14 AWG). Available in quantities of 10, 25 and 100.

**No wire stripping needed.
Simply insert wires, twist and lock.**

PRODUCT NO.	GAUGE	QTY.
LSC1030C-CTR10	10	10
LSC1030C-CTR25	10	25
LSC1030C-BULK	10	100
LSC1230C-CTR10	12	10
LSC1230C-CTR25	12	25
LSC1230C-BULK	12	100
LSC1430C-CTR10	14	10
LSC1430C-CTR25	14	25
LSC1430C-BULK	14	100



FEATURES AND BENEFITS

- Exclusive 90-degree twist-lock design makes wire connections easy and keeps wires locked in place; Won't open during backfilling
- Internal blade means **NO WIRE STRIPPING**
- Clear view helps verify wires are inserted fully before locking
- Water-proof, corrosion-proof dielectric sealant protects wires and prevents breaks in the transmit signal across connections

INSTALLATION INSTRUCTIONS

Warranty valid only with use of Copperhead wire. Do not use with THHN/THWN or any stranded wire product.

1. To assist with strain relief, twist wires together approximately 8" from the connector
2. DO NOT strip jacket from wire
3. Connector is gauge specific; Verify wire gauge matches connector gauge
4. Insert wires into holes fully so they are visible in the clear cap
5. Twist connector closed until locked

Do not pull on wires after connection is made.

