

Work Pro® Series Gasoline – Direct Drive

Designed to easily handle tough cleaning jobs, the WP Series is great for blasting away mud and muck and is great for cleaning jobs on the farm or small business.



Pump:

Equipped with the Mi-T-M Pressure Relief Start which eliminates pressure build-up in the system | Brass manifold | Thermal relief valve | In-line water strainer | Built-in low pressure detergent injector

Frame:

Powder coated steel frame and base plate with 1¼-inch tube handles | 10-inch flat-free tires

Unit Includes:

Quick connect nozzles - 15°, 25° and detergent nozzle | 25-foot x ¾-inch wire-braided high pressure hose (50-foot on WP-3600 and WP-4200 models) | Professional-grade trigger gun | Two-piece, 36-inch lance

Limited Warranties:

1 year AR and Mi-T-M pumps | Kohler engine: 3 month, commercial / 2 year residential | Honda engine on WP-2500 and WP-3000 models: 3 month, commercial / 2 year, residential | Honda engine on WP-3200, WP-3600 and WP-4200 models: 3 year

Certification:

Intertek - Certified to UL-1776 (WP-2500 and WP-3000 models)

USAGE MODEL NO.	Residential WP-2500-4MHB	Residential WP-3000-0MHB	Residential/Commercial WP-3000-0MKB	Commercial WP-3200-0MHB / WP-3200-0MKB	Commercial WP-3600-0MHB	Commercial WP-4200-0MHB (pictured) / WP-4200-0MKB
PSI	2500	3000	3000	3200	3600	4200
GPM	2.3	2.3	2.3	2.4	2.8	3.4
DISPLACEMENT/ENGINE	160cc Honda GC160 OHC	187cc Honda GC190 OHC	196cc Kohler SH265 OHV	196cc Honda GX200 OHV 208cc Kohler CH270 OHV	270cc Honda GX270 OHV	389cc Honda GX390 OHV 429cc Kohler CH440 OHV
PUMP	Mi-T-M, axial	Mi-T-M, axial	Mi-T-M, axial	Mi-T-M, crankshaft	AR, crankshaft	AR, crankshaft
UNLOADER	Fixed pressure	Fixed pressure	Fixed pressure	Adjustable pressure	Adjustable pressure	Adjustable pressure
DIMENSIONS (LxWxH)	37x21x24.5in.	37x21x24.5in.	37x21x24.5in.	37x21x24.5in.	40x22.5x24.5in.	40x22.5x24.5in.
SHIP WT.	100 lb.	100 lb.	100 lb.	110 lb.	180 lb.	192 lb.
NET WT.	75 lb.	75 lb.	75 lb.	85 lb.	130 lb.	142 lb.

Consult factory for more information on these available options:

- 25-foot high pressure hose with quick connects
- 50-foot high pressure hose, with and without quick connects