

Resistor™



CSA Z94.2-15 Class AL
Style - Disposable
NRR - 32
Shape - Tapered Bullet
Color - Orange
Dielectric - Yes
Material - Polyurethane Foam
Size - Regular

FP70BG50 - Uncorded - 50pr Bag

FP70 - Uncorded - 200 Box / 2000 Case
FP71 - Corded - 100 Box / 1000 Case

Resistor™



CSA Z94.2-15 Class BL
Style: Reusable
NRR: 27
Shape: 4 Flange Tapered
Color: Orange
Dielectric: Yes
Size: Regular

FP41 - Corded - 100 Box / 1000 Case

RAD)BAND 2

BANDED HEARING PROTECTION

CSA Z94.2-15 Class BL
Style - Reusable
NRR - 25
Shape - Pronged
Color - Orange
Dielectric - Yes
Material - Polyurethane Foam
Size - Regular



RB2100 - Orange Band / Orange Pods



CUSTOM MOLDED EARPLUGS

Molds in 10 minutes
Soft, Permanent, Custom Fit
All Day Comfort
Easy to Follow Instructions
Safe, Non-toxic
Hypo-allergenic
Environmentally Friendly
Long Lasting and Washable



CEP002-B Blue Box
CEP002-T Tan Box
CEP002-R Red Box



SILENCER™

Rugged construction
Dielectric design
Padded headband

Individually Packed
in a Resealable Polybag



SLO1301D - Black and Red



CAP MOUNT

CSA Z94.2-15 Class B
Universal design
Fits virtually all slotted hard hats
Adjustable side wire guides
Soft, foam padded earcups




*Hard hats sold separately

CMT26 - Black Earcups



CSA Z94.2-15 Class AL
Adjustable Moisture Wicking Headband
Folding Feature



TR0160CS - Black

