

# MECHANICAL JOINT GASKET

## Product Features

- Material - SBR
- Standard - ANSI / AWWA C111 / A21.11
- ASTM Test Methods
  - Hardness - D2240-91
  - Tensile Strength & Elongation - D412-92
  - Minimum Aging - D572-88
  - Maximum Compression - D395-89
- NSF/ANSI Standard 61 Compliant


## Product Specifications

### Transition

PART #	SIZE
<b>IMJTGM</b>	3"
<b>IMJTGP</b>	4"
<b>IMJTGU</b>	6"
<b>IMJTGX</b>	8"
<b>IMJTG10</b>	10"
<b>IMJTG12</b>	12"

### Gasket

PART #	SIZE
<b>IMJGAM</b>	3"
<b>IMJGAP</b>	4"
<b>IMJGAU</b>	6"
<b>IMJGAX</b>	8"
<b>IMJGA10</b>	10"
<b>IMJGA12</b>	12"
<b>IMJGA14</b>	14"
<b>IMJGA16</b>	16"



PROSELECT Glands, Gaskets, T-head Bolts and Mechanical Joint Accessory Packs are sold exclusively through Ferguson Enterprises and its affiliates.

Ferguson Enterprises guarantees the quality and compliance to the listed specifications.

PROSELECT is a registered trademark of Ferguson Enterprises.

## Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.

